




# P2



# P1

PIN OUT		
P1	568B Color	P2
1	White/Orange	1
2	Orange	2
3	White/Green	3
4	Blue	4
5	White/Blue	5
6	Green	6
7	White/Brown	7
8	Brown	8



20 cables per carton

1	2	3	4
BLU WH/BLU	ORG WH/ORG	GRN WH/GRN	BWN WH/BWN

**Material:**

- 4X2, 24AWG, twisted pair, 7\*0.19±0.15MM  
- OD: 5.2MM±0.30MM
- Insulation: HDPE-8380
- Jacket: PVC
- Contact Plug: UTP RJ45, 50µ"
- 568B Color wire standard
- Molded snaglass boot with strain relief
- Spot length on boot
- Connection 1:1



Scale	1:1						Name
TOLERANCE					Drawn	12.13.11	Chappell
X.X	±0.40				Approved		
X.XX	±0.25						
X.XXX	±0.15						
Angle	±3°						
Modification				Date	Name		



Item No.		<b>DK-1511-100/B</b>
Title		Cat 5e Patch Cord - Unshielded, Booted, UTP, 24AWG, Contact Plating 50µ" of Gold, Blue, 100 Feet
Drawing No.		
Replace	rev00	
Sheet		