



Product 14/40

[Previous](#)

[Product Listing](#)

[Next](#)



[larger image](#)
[larger image](#)

USB 2.0 cable - Hi-Speed, A/M ⇔ A/M, Shielded, Black, 3 Meters

Part Number: **AK670/2-3-BLACK**

More Information:

[>> Contact AWSW](#)

Purchase Through Distribution:



[Product Specification sheet](#)

Product Information:

Previously known as: **AK670/2-3-BLACK-R**

Hi-Speed USB 2.0 cable

- **Type A Male to type A Male connection**
- **Shielded**
- **Color: Black**
- **3 Meters**
- **4 pin**



Material:

- Cable: Black USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
- Connectors: USB 2.0 A Male Nickel PIN G/F 3PCS Type Insulator color: White
- Outer jacket: Black PVC-40P

Electrical:

- 100% short, open, miswire test
- Conduct resistance: 2Ω max.
- Insulation resistance: 10MΩ min.
- Dielectric test: DC 300V

Assmann WSW links

- [Assmann WSW components](#)
- [Assmann Germany](#)
- [Assmann Custom cables](#)
- [RoHS Compliance](#)
- [Product Change Notification](#)
- [End Of Life Notification](#)
- [Conflict Free Minerals Declaration](#)
- [Assmann mail](#)
- [Advanced Search](#)



USB 2.0 cable - Hi-Speed, A/M ⇌ A/M, Shielded, Black, 3 Meters

[Shipping & Returns](#) | [Privacy Notice](#) | [Contact AWSW](#) | [Site Map](#)



Your IP Address is: 35.164.3.180



Assmann WSW components, Inc.
1840 W. Drake Drive, Suite 101, Tempe, AZ. 85283
Phone: 877-277-6266 • www.Assmann.us

Copyright © 2006-2018 Assmann WSW components, Inc.. All rights reserved.