



PART FINDER

FIND NOW

Find faster what you're looking for!

Product Overview

Connectors

Thermal management

Cable assembly

Customer specific solutions

▶ **Power cords**

D SUB cable assembly

Modular cable assembly

USB cable assembly

USB Type C

Audio- & video cables

SATA cable

Flat ribbon cable

FFC cable

Capabilities



PDF download technical drawing

Power cords

A-PC2302-030026-1
External Power Supply cable - SJT 14 AWG, 60°C, Unshielded, NEMA 5-15P to IEC 320-C13 connectors, 120 V, 18 Amp, 3m, black

| | |
|---------------------------|------------------------------|
| Part number: | A-PC2302-030026-1 |
| product group: | Power cords |
| style: | External Power Supply cable |
| cable type: | SJT 14 AWG, 60°C, Unshielded |
| connector 1st end: | NEMA 5-15P |
| connector 2nd end: | IEC 320-C13 |
| length: | 3,00 |
| approvals: | UL certified |
| temperature: | 60°C |
| color: | black |
| packing: | bulk |



Electronica 2016
Please visit us and our Fidus at the Electronica in Munich Hall B2, Booth 560.

[MORE NEWS](#)



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, 85283, USA
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)

