



Powering Business Worldwide

#### 49-01BK-BU

Recp SnapIn 15A125V2P3W Tab&Scr Mclip BK

UPC: 032664594564

Brand Name: Eaton  
Sub Brand: Eaton  
Type: Angele Plug  
Special Features: Non Pol  
Application: Industrial  
Number Of Poles: 2  
Number Of Wires: 2  
Wire Size: 18 To 10 AWG  
Amperage Rating: 15Amp  
Voltage Rating: 125 Vac  
Material: Angle Super Plug  
Color: Black  
Mounting: Plug  
Connection: Plug

#### 49-01W-BU

Recp SnapIn 15A125V2P3W Tab&Scr Mclip WH

UPC: 032664594571

Brand Name: Eaton  
Sub Brand: Eaton  
Type: Easy Plug  
Special Features: Plug Easy Install-Polar  
Application: Industrial  
Number Of Poles: 2  
Number Of Wires: 2  
Wire Size: 18 To 10 AWG  
Amperage Rating: 10 Amp  
Voltage Rating: 125 Vac  
Material: Plug Easy Install  
Color: Brown  
Mounting: Plug  
Connection: Plug



Powering Business Worldwide

#### 49-21BK-BU

Recp SnapIn 15A125V2P3W WireLds Mclip BK

UPC: 032664594601

Brand Name: Eaton

Sub Brand: Eaton

Type: Easy Plug

Special Features: Plug Easy Install-Polar

Application: Industrial

Number Of Poles: 2

Number Of Wires: 2

Wire Size: 18 To 10 AWG

Amperage Rating: 10 Amp

Voltage Rating: 125 Vac

Material: Plug Easy Install

Color: Brown

Mounting: Plug

Connection: Plug

#### 49-2BK-BU

Recp SnapIn 15A125V2P3W WireLds Pclip BK

UPC: 032664357800

Brand Name: Eaton

Sub Brand: Eaton

Type: Easy Plug

Special Features: Plug Easy Install-Polar

Application: Industrial

Number Of Poles: 2

Number Of Wires: 2

Wire Size: 18 To 10 AWG

Amperage Rating: 10 Amp

Voltage Rating: 125 Vac

Material: Plug Easy Install

Color: Brown

Mounting: Plug

Connection: Plug



Powering Business Worldwide

**49-2W-BU**

Recp SnapIn 15A125V2P3W WireLds Pclip WH

UPC: 032664201509

Brand Name: Eaton

Sub Brand: Eaton

Type: Easy Plug

Special Features: Plug Easy Install-Polar

Application: Industrial

Number Of Poles: 2

Number Of Wires: 2

Wire Size: 18 To 10 AWG

Amperage Rating: 10 Amp

Voltage Rating: 125 vac

Material: Plug Easy Install

Color: White

Mounting: Plug

Connection: Plug

**49-4BK-BU**

SNAPIN GRD OUTLET

UPC: 032664594663

Brand Name: Eaton

Sub Brand: Eaton

Type: Cord End Single Polar

Special Features: Connector Cord End Polar

Application: Industrial

Number Of Poles: 2

Number Of Wires: 2

Wire Size: 18 To 10 AWG

Amperage Rating: 10 Amp

Voltage Rating: 125 Vac

Material: Connector Cord End

Color: Brown

Mounting: Plug

Connection: Plug



Powering Business Worldwide

#### 49-7BK-BU

Recp SnapIn 15A125V2P3W ParTabs Pclip BK

UPC: 032664594694

Brand Name: Eaton

Sub Brand: Eaton

Type: Cord End Single Polar

Special Features: Connector Cord End Polar

Application: Industrial

Number Of Poles: 2

Number Of Wires: 2

Wire Size: 18 To 10 AWG

Amperage Rating: 10 Amp

Voltage Rating: 125 Vac

Material: Connector Cord End

Color: White

Mounting: Plug

Connection: Plug

#### 49-81BK-BU

Recp SnapIn 15A125V2P3W 90DTabs Mclip BK

UPC: 032664594724

Brand Name: Cooper Wiring Devices

Special Features: Fits 2 and 3 Prong recepticles

Application: Child Safty Cap

Material: Thermoplastic CL

Color: Clear

#### 49-8BK-BU

Recp SnapIn 15A125V2P3W 90DTabs Pclip BK

UPC: 032664594717

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (2) Duplex Receptacle & Blank

Special Features: Standard Size Extra Delph Walplates

Application: Residential

Size: Standard, 2.75 In Width X 4.50 In Height

Gang: 2

Cutout: 2.15 In Hole Diameter

Material: Thermoplastic

Color: Ivory/White

Mounting: Screw

Construction: Standard Size Extra Delph Walplates



Powering Business Worldwide

#### 49BK-BU

Recp SnapIn 15A125V2P3W Tab&Scr Pclip BK

UPC: 032664357206

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (2) Toggle & Blank

Special Features: Standard Size Extra Delph Walplates

Application: Residential/Commercial

Size: Standard, 2.75 In Width X 4.50 In Height

Gang: 2

Cutout: 2.15 In Hole Diameter

Material: Thermoplastic

Color: White

Mounting: Screw

Construction: Standard Size Extra Delph Walplates

#### 49W-BU

Recp SnapIn 15A125V2P3W Tab&Scr Pclip WH

UPC: 032664201301