

([HTTP://WWW.BKPRECISION.COM](http://www.bkprecision.com))



# Datalogging Humidity/Temp Meter with Dual Input Model 725

MSRP \$389 / 1 Yr Warranty

[Where to Buy \(/w here-to-buy.html?invnt\\_id=725\)](#)



[Overview](#)

[Docs & Software](#)

[Accessories](#)



Testlink Software w/RS-232 Cable

## Model AK 720

MSRP \$49.00

---



Power Adapter, 9V DC 100mA

## Model BE 9

- UL & cUL Listed
- Barrel Jack Dimensions: 11mm long, 3mm diameter, 1mm internal diameter

MSRP \$13.75

---



Thermocouple Bead Probe, -50 to 200 C

## Model TP 29

Replacement thermocouple temperature probe for meters with K-type thermocouple inputs. PTFE insulated wire with exposed junction allows for fast air, gas, or general purpose measurements.

MSRP \$9.50

---

B&K Precision Corporation © 2016

[News & Media \(/news.html\)](#) [Contact Us \(http://www.bkprecision.com/contact-us.html\)](http://www.bkprecision.com/contact-us.html)

[Distributor Tools \(https://www.bkprecision.com/distributor-access.html\)](https://www.bkprecision.com/distributor-access.html) [Site Map \(/sitemap.html\)](#)