

AC Current Clamp Meter with Bargraph, 1000A Model 350B

Overview

Docs & Software

Accessories

Where to Buy



Clamp-On DMM Carrying Case

Model LC 33

- Made in the U.S.A.
- Light weight, durable Cordura nylon
- Protects your instruments
- Room to hold your test leads
- Approximate Internal Dimensions: 5 x 1.75 x 10.5" (127 x 44 x 267mm)



General Purpose DMM Kit

Model TL130B

If you need only one basic accessory kit for your meter, this is the one. Attach probes or clips to the sheath plug to complete your test. Soft, flexible silicone leads make movement easy. Kit is voltage and current rated for electronic or electrical applications.

- Probes are 1000 V, CAT III (600 V, CAT IV)
- Alligator clips are 300 V, CAT II 5A
- UL Listed test leads
- Silicone lead wire length 60" (1.5 m)
- Tri-fold velcro pouch



Red and Black CAT III (IV) 1000V (600V) Test Leads

Model TL37

Right angled sheathed banana replacement 10A test leads for digital multimeters. With tip cap on, they are rated to CATIII 1000V, CAT IV 600V, with tip cap off, they are CAT II 1000V.



Maxi-Pro DMM Kit

Model TL50B

- Complete accessory kit for all your testing needs.
- Includes soft, flexible silicone lead wire easy movement and Tri-Fold Velcro Pouch for convenient storage.
- 1000 V, CAT III (600 V, CAT IV)
- UL Listed test leads
- Silicone lead wire length 60" (1.5m)
- Tri-fold Velcro Pouch

