



[Back](#)

Selected Cable: 17250 10 B1					Cord View
End View	Plug	Cord	Connector	End View	No Picture Available.
5-15P	290B	SVT	386	C13	
<b>Part Number</b>	<b>17250 10 B1</b>				
<b>NSN</b>	6150-01-004-8773				
<b>Category</b>	3 conductor plastic detachable				
<b>Shielding</b>	unshielded				
<b>Jacket Color</b>	black or beige				
<b>Length Feet</b>	7'6"				
<b>Length Meters</b>	2.29				
<b>Temperature Rating</b>	60 C°				
<b>Packaging Units Per Carton</b>	H-100,H-25,S-25				
<b>Color Coding</b>	North America				
<b>AWG Stranding</b>	18 (41x34)				
<b>Nominal OD Inch</b>	0.246				
<b>Nominal OD millimeter</b>	6.25				
<b>Rating</b>	1250 Watts 10A-125V				
<b>Notes</b>	SEE ALSO THE 17249 FOR A 6FT VERSION. Same as 17251 except for color code.				
					<b>Approvals</b>

**RoHS Compliant**

YES



Qty:

**Back**

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

