





[Back](#)

Selected Cable: 17422

End View	Plug	Cord	Connector	End View
				
5-15P	185	SJ	3"STRIP	NONE

Part Number	17422
Category	2 and 3 conductor rubber original equipment cords
Shielding	unshielded
Jacket Color	black
Length Feet	12'
Length Meters	3.66
Temperature Rating	60 C°C
Packaging Units Per Carton	B-25,S-15
Color Coding	North America
AWG Stranding	16 (26x30)
Nominal OD Inch	0.34
Nominal OD millimeter	8.64
Rating	1625 Watts 13A-125V
Notes	See 17419 for 9ft version. See 17425 for 15ft version. See 17412 for 18 gauge version.

Cord View



Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

