




**Back**

**Selected Cable: 17568**

End View	Plug	Cord	Connector	End View
6-15P	32	SJT	386A	C13

**Cord View**



<b>Part Number</b>	17568
<b>Category</b>	3 conductor plastic original equipment cords
<b>Shielding</b>	unshielded
<b>Jacket Color</b>	black
<b>Length Feet</b>	6'7
<b>Length Meters</b>	2
<b>Temperature Rating</b>	60 C°C
<b>Packaging Units Per Carton</b>	H-25
<b>Color Coding</b>	International
<b>AWG Stranding</b>	18 (41x34)
<b>Nominal OD Inch</b>	0.315
<b>Nominal OD millimeter</b>	8
<b>Rating</b>	2500 Watts,10A-230V
<b>Notes</b>	The plug on this cord was recently changed from the PH44 to the AEC32. See 17566 for SVT version.

**Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

