



SEARCH VOLEX...



OUR MARKETS >

OUR PRODUCTS >

Power cords

Industry standard cable assemblies

High speed cable assemblies

Radio frequency cable assemblies

Healthcare products and solutions

Imaging systems

Clinical diagnostics systems

Medical therapy systems

OUR CAPABILITIES >

VOLEX WORLDWIDE >

INVESTOR RELATIONS >

ABOUT VOLEX >

Standard cord details: 17038A 10 C3

[View PDF Drawing](#)

[Check Stock](#)



Specifications

Certifications	UL, CSA
Part Number	17038A 10 C3
Connector Type	C7
Plug Type	1-15P
Category	Plastic
Application	Detachable
Plug Catalog No.	ME301S
Connector Catalog No.	
Cable	SPT-2 AWG 18x2
Jacket Color	Black
Length in Feet	6.6
Length in Meters	2
Temperature Rating	60C
Packaging Units Per Carton	25
Color Coding	North America
Nominal OD in Inches	.144x280
Nominal OD in Millimeters	3.66x7.11
Notes	See 17036 for C5 connector version.

[← BACK](#)