


VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.



NOTES

- 1) CORDAGE: 26AWG, 7 CONDUCTOR, PVC, FOIL WRAP/SPIRAL SHIELD, 80°C, BLACK
- 2) COPPER CONDUCTOR TO BE MADE UP OF 19 STRANDS OF 38AWG TINNED COPPER.
- 3) JACKETED SINGLES WILL BE BLACK, WHITE, RED, GREEN, BROWN, BLUE, AND ORANGE IN COLOR.
- 4) CORDAGE D.D.: .250" NDM.
- 5) APPROVALS: UL AWM 2464
- 6) RATING: 300 VOLTS
- 7) CARTON QTY TBD.
- 8) ALL DIMENSIONS IN INCHES UNLESS OTHERWISE SPECIFIED.

CUD

FORM IN71-07 REV.A

Indianapolis, IN
 Conover, N.C.
 Freemont, CA
 Aguascalientes, MX
 Tijuana, Mexico
 Hermosillo, MX
 Clinton, AR
 Kanata, Canada

Proprietary Notice:
 This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

ROHS COMPLIANT
 FINISH: JACKET: SMOOTH

SCALE:	ECD:	ITEM DESCRIPTION	DATE
NDT TD SCALE	N/A	PRELIMINARY RELEASE	12/19/08
DESCRIPTION			
RETRACTILE CORD - NORTH AMERICAN			
APPROVED	DRAWN BY	DATE	
MAF	MAF	12/19/08	
PART NO.	6665		

TOLERANCE UNLESS OTHERWISE SPECIFIED
 .XXX ± .005
 .XX ± .02
 .X ± .03
 FRACT. ± 1/32°
 ANGULAR ± 1/2°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Volex:](#)

[6665 10 1](#)