



[CONNECTORS](#)

[DIP SOCKETS](#)



✓ Active

TE CONNECTIVITY (TE)

322-HCS5P2-308=" REEL ASSY.,500

[HOLTITE](#) | [HOLTITE](#)

322-HCS5P2-308

TE Internal Number: 2-1437514-4

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Contact Style Screw Machine

Number of Positions 8

Profile Zero

Row-to-Row Spacing 7.62 mm [.3 in]

Mounting Angle Vertical

DOCUMENTATION

[Product Specifications](#)

[Application Specification](#)

AUGAT HOLTITE Sockets

PDF

English

[Product Specification](#)

AUGAT HOLTITE Sockets

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Profile Zero

Row-to-Row Spacing 7.62 mm [.3 in]

Leg Style Straight

Product Type Socket

Configuration Features

Number of Positions 8

Electrical Characteristics

Insulation Resistance (MΩ) 1000

Body Features

Frame Style Film Carrier

Carrier Strip Material Mylar

Contact Features

Contact Style Screw Machine

Contact Mating Area Plating Material Gold

Contact Mating Area Plating Thickness (μin) 25

Contact Current Rating (Max) (A) 3

Mating Contact Type Four-Fingered

Contact Type Socket

Contact Base Material Beryllium Copper

Socket Style Standard

Socket Type DIP

Termination Features

Contact Termination Type Through Hole

Termination Post Length 3.18 mm [.125 in]

Mechanical Attachment

Mounting Angle Vertical

PCB Mount Retention Without

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]

Dimensions

Height above PC Board 0 mm [0 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Packaging Features

Packaging Quantity 5000

Packaging Method Reel

Other

Patterns Per Reel 625

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
