


FSP-24A-10 Product Details

[Live Product Chat](#)



FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- 2.54 mm Centerline
- Polyester Insulation Material
- Insulation Length = 101.60 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

FSP-24A-10
(7-1437167-9)

TE Part Number: 7-1437167-9

[Active](#)

[Add to Part List](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product View](#)
- [Product View](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Insulation Material](#) = Polyester
- [Number of Conductors](#) = 10

Electrical Characteristics:

- Current Rating (Amps.) = 3
- Impedance (Ω) = 113
- Voltage Rating (VAC) = 300

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- [Insulation Length \(mm \[in\]\)](#) = 101.60 [4.000]

Configuration Related Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +105 [-40 - +221]

Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Need Help?](#)