

## 8PCV -02 Product Details




**8PCV -02**

TE Part Number: 5 - 1437657 -2

 **Superseded**

[Add to Part List](#)  
[Search for Replacement Parts](#)

### Barrier Strips, Barrier Strip Sockets

[Not reviewed for RoHS Compliance](#)

#### Product Highlights:

- ? Barrier Strip
- ? Barrier Style = Single Row, Tri -Barrier
- ? Block Style = Open Bottom with Standoffs
- ? 11.10 mm Centerline
- ? Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

### Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling](#)  
[Product Feature Selector](#)  
[Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? None Available

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Barrier Strip
- ? [Mount Angle](#) = Vertical
- ? Number of Positions = 2
- ? CSA File No. = LR30811
- ? UL Recognized = File No. E54800
- ? Screw Material = Steel
- ? Mounting Ears = Without
- ? Comment = Do not order Screw and Captive Clamp in combination with other top hardware.; Other options available upon request, consult our Product Information Center.

#### Mechanical Attachment:

- ? Screw Plating = Zinc Chromate
- ? Mounting Style = Direct (All Positions Filled)

#### Electrical Characteristics:

- ? [Top Hardware](#) = Wire Clamp Combo Head
- ? Number of Levels = Single
- ? End Barriers = Without
- ? Bracket = Without
- ? Current Rating (Amps.) = 30
- ? Screw Head Type = Slotted
- ? Voltage (VAC) = 600
- ? Mounting Insert = Without

#### Termination Related Features:

- ? Terminal Plating = Bright Tin

#### Body Related Features:

- ? [Barrier Style](#) = Single Row, Tri -Barrier
- ? Block Style = Open Bottom with Standoffs
- ? [Centerline \(in \[mm\]\)](#) = 0.4375 [11.10]
- ? Number of Rows = Single
- ? [Terminal Style](#) = Printed Circuit Pin 5.08 [.200]
- ? Terminal Material = Copper Alloy

#### Contact Related Features:

- ? Mounting Options = None

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

#### Other:

- ? Brand = Buchanan