
# **Pre-Printed Wire & Cable Markers**

#### BradyID.com



# **Pre-Printed Wire & Cable Markers**

Brady offers wire and cable markers in pre-printed number and letters for use in electrical applications. These wire marker cards come in several materials and styles for a variety of applications.

### B-500 Vinyl Porta-Pack® Wire Marker Books

Repositionable vinyl cloth Porta-Pack books are a convenient way to ensure the wire markers you need are always on hand. Slim, lightweight, pocket-sized book is easy to carry and are available in a large selections of legends. Each book comes with 10 pages and includes a terminal marker with each wire marker.

Catalog #	Legend	Marker Quantity of Each Legend	Pages Per Book
PWM-PK-1	0 thru 9	45	10
PWM-PK-2	A thru Z, 0 thru 15, (+), (–), (/)	10	10
PWM-PK-3	1 thru 45	10	10
PWM-PK-4	1, 2, 3	150	10
PWM-PK-5	A, B, C	150	10
PWM-PK-6	T1, T2, T3	150	10
PWM-PK-7	L1, L2, L3	150	10
PWM-PK-8	1 thru 15 16 thru 90, A–Z, (+), (–), (/), (0)	6 4 2	10
PWM-PK-9	1, 2, 3, A, B, C T1, T2, T3, L1, L2, L3	45 30	10
PWM-PK-10	10 different NEMA colors	45	10
PWM-PK-11	1 thru 30	15	10
PWM-PK-12	A thru Z Blank Write-On Labels (+) (–)	15 18 8 9	10
PWM-PK-13	(+), (–),AC, DC POS, NEG, GND, NEUT Spare Blank Write-On Labels	45 33 21 21	10
PWM-PK-14	46 thru 90	10	10
PWM-PK-15	1 thru 45 46 thru 90	5 5	10



## B-292 Write-On Self-Laminating Wire & Cable Markers

- Use labeling pens or other markers to write on your legend
- Transparent part over-wraps provide snug fitting, self-laminating shield that resists oil, water and solvents
- For applications above or below ground

Catalog #	Legend	Marker Size Inch (mm)	Write-On Area Inch (mm)	Markers Per Book
PWC-PK-1	Blank/Write-on	0.750 x 1.750 (19.000 x44.40)	0.750 x 0.500 (19.00 x 12.70)	120
PWC-PK-3	Blank/Write-on	1.000 × 3.000 (25.40 × 76.20)	1.000 × 0.750 (25.40 × 19.00)	60
PWC-PK-6	Blank/Write-on	1.000 x 6.000 (25.40 x 152.40)	1.000 x 1.000 (25.40 x 25.40)	30
PWC-PK-36	Blank/Write-on	1.000 x 3.000 (25.40 x 76.20) 1.000 x 6.000 (25.40 x 152.40)	1.000 x 0.750 (25.40 x 19.00) 1.000 x 1.000 (25.40 x 25.40)	30 15

