



Plug Valve Lockout

- Ideal for difficult-to-secure plug valves in compliance with OSHA standards
- Four sizes to fit most 1" to 8" diameter manually-actuated plug valves
- Durable and tamper-resistant
- Service temps from -25°F to 200°F
- Compact in size and easy to use

Catalog #	Description
113231	Lockout for up to 7/8" Stem Dia.
113232	Lockout for 15/16" to 1-3/8" Stem Dia.
113233	Lockout for 1-3/4" to 2-1/8" Stem Dia.
113234	Lockout for 2-3/16" to 2-1/2" Stem Dia.



Adjustable Gate Valve Lockout

- Versatile lockout adjusts to fit 1" to 6-1/2" valve handles, replacing 3 conventional gate valve lockouts
- Constructed of rugged injection-molded polypropylene
- Service temps from -13°F to 194°F
- Supplied with English, Spanish and French danger labels

Catalog #	Description
64057	Adjustable Gate Valve Lockout



Gate Valve Lockouts

- Unique knockout center fits OS&Y or "rising stem" valves
- Made of rugged injection-molded polypropylene
- Service temps from -25°F to 200°F
- Accepts shackles up to 3/8" in dia.
- Supplied with English, Spanish and French danger labels


Fits Valve Handles Dia.	Red	Yellow	Green	Blue
1" to 2-1/2"	65560	65590	65595	65585
2-1/2" to 5"	65561	65591	65596	65586
5" to 6-1/2"	65562	65592	65597	65587
6-1/2" to 10"	65563	65593	65598	65588
10" to 13"	65564	65594	65599	65589



Prinzing Ball Valve Lockout

- Made from ultra-tuff polypropylene
- Small size locks out pipes 1/2" to 2-1/2" in diameter
- Small size can also lock valves OPEN on pipes from 1/2" to 1-1/4" in diameter
- Large size locks out pipes 2" to 8" in diameter

Catalog #	Size	Color
BS07A-RD	Small	Red
BS08A-RD	Large	Red
BS07A-BU	Small	Blue
BS08A-BU	Large	Blue
BS07A-GN	Small	Green
BS08A-GN	Large	Green
BS07A-YW	Small	Yellow
BS08A-YW	Large	Yellow



Standard Ball Valve Lockout

- Easy to use, single-piece design locks quarter-turn ball valves in OFF position
- Two sizes fit most valves up to 3"
- 65666 is made of super-tough nylon (service temp -40° to 248° F)
- 65692, 65669 and 65693 are made of powder-coated steel

Catalog #	Max Shackle Dia.	Valve Size / Pipe Dia.	Max Handle Width	Max Handle Thickness
65666	932"	1/4" to 1"	1-1/2"	3/4"
65692	38"	1/4" to 1"	1-1/2"	3/4"
65669	932"	1-1/4" to 3"	2-1/10"	1 1/4"
65693	38"	1-1/4" to 3"	1-9/10"	1 1/4"



Perma-Mount™ Ball Valve Lockout

- Retrofit devices stay permanently in place at the point of need
- One-time installation is easy to complete in just a few minutes
- Available in 2 sizes to fit a full range of 0.5" to 4" diameter ball valves

Catalog #	Size
121540	Small Perma-Mount Ball Valve Lockout
121541	Large Perma-Mount Ball Valve Lockout

