

[Printers and Scanners / Desktop Printers, Labels and Accessories / BBP12 Label Printer, Labels and Accessories / BBP12 Label Printer Labels /](#)

[1" Core Series Paper Labels](#)



## 1" Core Series Paper Labels

**Part Number:**

THT-17-424-1.5-SC

**Label/Tape Size (in/ft/yd):**

1 in H x 2 in W

**Material:**

Paper

**Brady Material Number:**

B-424

**Color:**

White

**Quantity per Roll:**

1500

**For Use with Printer:**

BBP®11 Label Printer, BBP®12 Label Printer, BRADY 1244 Series Label Machine, BRADY 1344 Series Label Machine

**ADD TO CART**

1

# OVERVIEW

Paper Labels with Permanent Rubber Adhesive (B-424) provide good contrast and smear resistance for thermal transfer and barcode printing applications.

- White matte paper label stock features permanent rubber adhesive
- Low cost is ideal for all general purpose labeling projects
- RoHS compliant to EU directive 2011/65/EU
- Service temperature of -40 to 122° F (-40 to 50° C)

# SPECIFICATIONS

Brady Material Number	<b>B-424</b>
Dimensions	1 in H x 2 in W
Display UoM	Roll of 1500 Labels
Indoor or Outdoor Use	Indoor Use
Label/Tape Size (in/ft/yd)	1 in H x 2 in W
Maximum Service Temperature °F	122 °F
Minimum Service Temperature °F	-40 °F
Printable Area Dimensions	1 in H x 2 in W
Printable Area Height (in/ft/yd)	1 in
Printable Area Width (in/ft/yd)	2 in
Product Number	114194
UPC	662820920991
Quantity per Roll	1500
Quantity per Row	1
Secondary Label Included	Secondary Label is Not Included
Thickness (in/ft/yd)	0.0035 in
Adhesive Type	Permanent Rubber Based
Applications	General & Industrial ID
Color	White
For Use with Printer	BBP®11 Label Printer, BBP®12 Label Printer, BRADY 1244 Series Label Machine, BRADY 1344 Series Label Machine

Label/Media Format	Roll
Material	Paper
Material Properties	Provides good contrast and smear resistance for thermal transfer and barcode printing
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Humidity-Resistant, Smear-Resistant, UV-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4300, R4500, R6100

## Solutions

[Floor Marking Guide](#)  
[GHS Label Compliance](#)  
[Lockout Tagout Compliance](#)  
[Arc Flash Labeling Requirements](#)  
[Cable and Wire Label Options](#)  
[Product and Barcode Labeling](#)

## Services

[Lockout Tagout Services](#)  
[Arc Flash Services](#)  
[Confined Space Services](#)  
[Visual Workplace Services](#)  
[Hazcom GHS Services](#)  
[Software Programming & Integration](#)  
[Label Template & File Conversion](#)  
[Printer Use & Training](#)  
[Printer Preventative Maintenance](#)  
[Toll and Custom Coating](#)

## Help

[Contact Us](#)  
[Knowledge Center](#)  
[Printer Drivers & Firmware](#)  
[Brady Software Updates](#)  
[Safety Data Sheets](#)  
[Technical Data Sheets](#)  
[WEEE RoHS Compliance](#)  
[Product Certification](#)  
[Printer Registration](#)

## Resources

[Find a Distributor](#)  
[Printer Selection Tool](#)  
[Label Selection Tool](#)  
[Digital Catalog](#)  
[Request a Catalog](#)



**Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance**

### Contact About

**6555 W. Good Hope Rd. Milwaukee, WI 53223**  
**Phone: 888-250-3082**  
**Hours: 7am-6pm CST**  
**Monday - Friday**

### Other

[Brady Sites](#)  
[Distribution Portal International](#)  
[Safety Services & Software Smart ID Brand Protection](#)

[Privacy Policy](#)  
[Terms and Conditions](#)  
[Terms of Use](#)



© 2017 Brady Worldwide, Inc.

**labels,  
signs, safety  
devices,  
printing  
systems  
and  
software.**