

DANGER High Voltage Sign

DANGER High Voltage Sign



Product Highlights:

Sign Size (H x W):

2.25" x 4.5"

Material:

Polyester

Part Number:

89173

ADD TO CART

1



PEOPLE WHO VIEWED THIS ITEM ALSO VIEWED

OVERVIEW

B-302 is an indoor/outdoor high performance pressure sensitive safety sign, and is surface printed polyester with a polyester overlamine.

- Weathers up to 8 years outdoors, even longer indoors, and withstands wide temperature variations (up to 230°F)
- Flexible material conforms to most surfaces while protected graphics hold up to harsh environments, abrasion, and repeated spills and cleanings
- Permanent, pressure sensitive adhesive forms a long-lasting bond to even the most difficult surfaces and shapes
- Cold temperature adhesive allows the signage to be applied at 0°F (-18°C)

SPECIFICATIONS

Material Number	B-302
Catalog Page #	93
Dimensions	2.25 in H x 4.5 in W x 0.006 in D
UOM	Each
Illumination	Not Illuminated
Indoor or Outdoor Use	Outdoor Use
Laminated	Laminated
Maximum Service Temperature °F	230 °F
Minimum Service Temperature °F	-40 °F
PSPA Photoluminescence Class	Not Illuminated
Product Number	89173
UPC	754473891732
Reverse Legend	No Reverse Text
Sign Size (H x W)	2.25" x 4.5"
Thickness	0.01 in
Adhesive Type	Acrylic

Color	Black/Red on White
Header	DANGER
Language	English
Material	Polyester
Meets Industry Standards - Signs	ANSI Z53.1-1967
Mounting Type	Self-Adhesive
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant
Reverse Header	No Reverse Header
Shape	Rectangle
Text Legend	HIGH VOLTAGE

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO](#)
[Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Smart ID Brand Protection Solutions](#)

6555 W. Good Hope Rd.
 Milwaukee, WI 53223
 Phone: 888-250-3082
 Hours: 7am-6pm CT
 Monday - Thursday;
 Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.