



3440 Series Repositionable Number and Letter Labels

3440 Series Repositionable Number and Letter Labels



Product Highlights

Text Legend:

7

Part Number:

3440-7



[Add To Favorites](#)

Overview

Permanent or repositionable: once applied, 34 Series numbers & letters are there to stay... unless you want to change them.

- Made of CleanLift® Series Vinyl Cloth (B-498) with repositionable rubber adhesive
- The adhesive and cloth backing offers excellent holding power, yet allow for clean removal and repositioning
- Sticks to any clean, dry surface
- Specially formulated topcoat for excellent print quality

Specifications

Material Number	B-498
Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Cards or Sheets per Pack	1
Catalog Page #	225
Character Height	2 in
Dimensions	2.25 in H x 0.875 in W x 0.0073 in D
UOM	Card of 10 Labels
Finish	Semi-gloss
Illumination	Not Illuminated

Maximum Service Temperature °F	176 °F
Minimum Service Temperature °F	-40 °F
National Stock Number (NSN)	9905009023030
PSPA Photoluminescence Class	Not Illuminated
Product Number	34407
UPC	754473344078
Quantity per Card or Sheet	10
Thickness	0.0073 in
UNSPSC	55121721
Adhesive Type	Repositionable Rubber
Applications	Cable & Wire Marking, General & Industrial ID
Color	Black on Yellow
Label/Media Format	Die-Cut on Cards
Label Properties	Repositionable Labels
Material	Cloth
Mounting Type	Self-Adhesive
Printer and Label Applications	Wire & Cable
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Text Legend	7

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Create Custom THT Labels](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

[Corporate](#) [Other Brady](#) [Contact](#)

[About](#)

[Careers](#)

[Investors](#)

[Privacy](#)

[Policy](#)

[Terms and](#)

[Conditions](#)

[Terms of](#)

[Use](#)

[ISO](#)

[Certificates](#)

[Sites](#)

[Distributor](#)

[Portal](#)

[International](#)

[Sites](#)

[Safety](#)

[Services &](#)

[Software](#)

[Brand](#)

[Protection](#)

[Solutions](#)

6555 W.

Good Hope

Rd.

Milwaukee,

WI 53223

Phone: 888-

250-3082

Hours: 7am-

6pm CT

Monday -

Thursday;

Friday 7am-

5pm CT

Brady (NYSE:BRC) is a

manufacturer of complete

solutions that identify and

protect people, products and

places. Brady's products help

customers increase safety,

security, productivity and

performance and include high-

performance labels, signs, safety

devices, printing systems and

software.



2019 © Brady Worldwide, Inc.