



**1.000 IN W X 0.250 IN H (25.400 MM W X 6.350 MM H) - # THT-103-728-10**

**SIZE:** 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)  
**MATERIAL:** Permanent Polyimide  
**QTY/UOM:** 10,000/Roll  
**CATALOG #:** THT-103-728-10  
**PRODUCT #:** 132501

**\$597.63** MSRP (\$US)  
 QTY:  **ADD TO CART >>**

[VIEW LARGER](#)

**Questions?**  
**1.888.250.3082**

**SPECIFICATIONS**


**Specification Of 1.000 IN W X 0.250 IN H (25.400 MM W X 6.350 MM H)**

**Application(s):** Circuit Board ID, Component ID, SMT - Top/Bottom, Through Hole - Bottom, Through Hole - Top  
**Agency Approval(s)/Compliance:** MIL-STD-202F, Notice 12, Method 215J; UL Recognized  
**Size:** 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)  
**Printable Area:** 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)  
**Web Width:** 1.200" (30.48 mm)  
**Vertical Repeat:** 0.350" (8.89 mm)  
**Color:** White  
**Finish:** Matte  
**Qty Per Row:** 1  
**Material Description:** Permanent Polyimide  
**Brady Material #:** B-728  
**General ID Catalog:** pg. 149  
**Recommended Ribbon Series:** R6000 & R6000HF  
**Acceptable Ribbon Series:** R4800  
**Print Technology:** Thermal Transfer  
**Printer Compatibility:** BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers  
**Style:** Label  
**Special Properties:** Excellent resistance to harsh fluxing and wave solder environments, Resists all commonly employed methods of cleaning  
**RoHS Compatibility:** Pass 2011/65/EU  
**QTY/UOM:** 10,000/Roll

<p>Customer &amp; Tech Support</p> <p><a href="#">Find a Distributor</a></p> <p><a href="#">Submit Product Feedback</a></p> <p><a href="#">Submit Website Feedback</a></p> <p><a href="#">Contact Us</a></p> <p><a href="#">Site Map</a></p>	<p>Distribution Partners</p> <p><a href="#">Bradyserve.com</a></p> <p><a href="#">BradyDistributor.com</a></p> <p><a href="#">Minimum Advertised Price Policy</a></p>	<p>Corporate Info</p> <p><a href="#">Bradycorp.com</a></p> <p><a href="#">Privacy Policy</a></p> <p><a href="#">Legal Information</a></p> <p><a href="#">ISO14001 Certified</a></p> <p><a href="#">ISO9001 Certified</a></p> <p><a href="#">Environmental Policy</a></p> <p><a href="#">Terms of Use</a></p> <p><a href="#">Terms and Conditions of Sale</a></p>	<p>Brady International Sites</p> <table border="0"> <tr> <td><a href="#">Canada</a></td> <td><a href="#">Brazil</a></td> <td><a href="#">Europe, Africa, Middle East</a></td> </tr> <tr> <td><a href="#">Canada (Français)</a></td> <td><a href="#">Asia</a></td> <td></td> </tr> <tr> <td><a href="#">Latin America</a></td> <td><a href="#">Australia</a></td> <td></td> </tr> </table>	<a href="#">Canada</a>	<a href="#">Brazil</a>	<a href="#">Europe, Africa, Middle East</a>	<a href="#">Canada (Français)</a>	<a href="#">Asia</a>		<a href="#">Latin America</a>	<a href="#">Australia</a>	
<a href="#">Canada</a>	<a href="#">Brazil</a>	<a href="#">Europe, Africa, Middle East</a>										
<a href="#">Canada (Français)</a>	<a href="#">Asia</a>											
<a href="#">Latin America</a>	<a href="#">Australia</a>											

Brady identifies and protects products, people, and premises with high performance labels, industrial label printers, software, safety & facility identification, spill control, Lockout Tagout solutions and more. Brady helps you create and maintain safer work environments and comply with regulatory standards. Our high-performance materials clearly identify products, components and other assets, even in the most extreme conditions.

**BRADY**  
©2015 Brady Worldwide, Inc.

Safe & Secure Online Shopping