

## Thermal Transfer Printable Labels- # THT-14-426-10



**SIZE:** 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)  
**MATERIAL:** High Temperature Polyimide  
**QTY/UOM:** 10,000/Roll  
**CATALOG #:** THT-14-426-10  
**PRODUCT #:** 30121

**\$391.79** MSRP (\$US)

QTY:

### PRODUCT SUPPORT

- Portable Label Printers
- Industrial Printers
- Label Design Software
- Printer Ribbons
- JetTab Set Up Sheets
- LaserTab Set Up Sheets

OVERVIEW SPECIFICATIONS

#### Description for Thermal Transfer Printable Labels

Printable, high temperature polyimide labels for thermal transfer printers.

#### Specification Of Thermal Transfer Printable Labels

**Application(s):** Circuit Board & Component ID, SMF Top/Bottom, Through Hole- Bottom, Through Hole- Top  
**Size:** 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)  
**Printable Area:** 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)  
**Web Width:** 2.950" (74.93 mm)  
**Label Type/Style:** Label  
**Vertical Repeat:** 0.300" (7.62 mm)  
**Horizontal Repeat:** 0.700" (17.78 mm)  
**Color:** Amber  
**Finish:** Matte  
**Qty Per Row:** 4  
**Material Type:** Polyimide  
**Material Description:** High Temperature Polyimide  
**Brady Material #:** B-426  
**General ID Catalog:** pg. 140  
**Recommended Ribbon Series:** 4300  
**Suggested Ribbon Part#:** R4300  
**After Process:** Yes, this material will work with this application  
**Printer Compatibility:** BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300MVPs II, Brady 3481, Brady 360XPlus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers  
**Surface Mount Technology:** Yes, this material will work with this application  
**Through Hole Technology:** Top: Yes, Bottom: Yes  
**Special Properties:** Withstands extremely high temperatures  
**RoHS Compatibility:** Compliant with RoHS DirectiveNOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.  
**QTY/UOM:** 10,000/Roll

Customer & Tech Support  
[Find a Distributor](#)  
[Submit Product Feedback](#)  
[Submit Website Feedback](#)  
[Contact Us](#)  
[Site Map](#)

Distribution Partners  
[Bradyserve.com](#)  
[BradyDistributor.com](#)  
[Minimum Advertised Price Policy](#)

Corporate Info  
[About Brady](#)  
[Bradycorp.com](#)  
[Privacy Policy](#)  
[Legal Information](#)  
[ISO Certified](#)  
[Terms of Use](#)  
[Terms and Conditions of Sale](#)

Brady International Sites  
 Canada Brazil Europe, Africa, Middle East  
 Canada (Français) Asia  
 Latin America Australia