



## Thermal Transfer Printable Labels- # THT-3-423-10

**SIZE:** 1.000" W x 0.375" H (25.400 mm W x 9.530 mm H)  
**MATERIAL:** Permanent Polyester  
**QTY/UOM:** 10,000/Roll  
**CATALOG #:** THT-3-423-10  
**PRODUCT #:** 30106

**\$98.21** MSRP (\$US)

QTY:

### PRODUCT SUPPORT

- [Portable Label Printers](#)
- [Industrial Printers](#)
- [Label Design Software](#)
- [Printer Ribbons](#)
- [JetTab Set Up Sheets](#)
- [LaserTab Set Up Sheets](#)

#### OVERVIEW

#### SPECIFICATIONS

### Description for Thermal Transfer Printable Labels

BradyBondz™ polyester labels for thermal transfer printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

### Specification Of Thermal Transfer Printable Labels

**Application(s):** Circuit Board & Component ID, Through Hole Top

**Agency Approval (s)/Compliance:** AGA Approved, CSA Approved, HalogenFree (DIN VDE 0472/parts 815), UL Recognized

**Size:** 1.000" W x 0.375" H (25.400 mm W x 9.530 mm H)

**Printable Area:** 1.000" W x 0.375" H (25.400 mm W x 9.530 mm H)

**Web Width:** 3.350" (85.09 mm)

**Label Type/Style:** Label

**Vertical Repeat:** 0.475" (12.07 mm)

**Horizontal Repeat:** 1.075" (27.31 mm)

**Color:** White

**Finish:** Gloss

**Qty Per Row:** 3

**Material Type:** Polyester

**Material Description:** Permanent Polyester

**Brady Material #:** B-423

**General ID Catalog:** [pg. 88](#)

**Recommended Ribbon Series:** 6000

**Suggested Ribbon Part#:** R6002

**Acceptable Ribbon Series:** 4900, 6200

**After Process:** Yes, this material will work with this application

**Printer Compatibility:** BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300Xs II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers

**Surface:** Smooth

**Surface Mount Technology:** No, this material does not work with this application

**Through Hole Technology:** Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

**RoHS Compatibility:** Compliant with RoHS DirectiveNOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 10,000/Roll

Customer & Tech Support  
[Find a Distributor](#)  
[Submit Product Feedback](#)  
[Submit Website Feedback](#)  
[Contact Us](#)  
[Site Map](#)

Distribution Partners  
[Bradyserve.com](#)  
[BradyDistributor.com](#)  
[Minimum Advertised Price Policy](#)

Corporate Info  
[About Brady](#)  
[Bradycorp.com](#)  
[Privacy Policy](#)  
[Legal Information](#)  
[ISO Certified](#)  
[Terms of Use](#)  
[Terms and Conditions of Sale](#)

Brady International Sites  
 Canada  
 Canada (Français)  
 Latin America  
 Brazil  
 Asia  
 Australia  
 Europe, Africa, Middle East