

How to Order — Plug

| Contact Style | Nomenclature | Part Number | Size | Type | No. of Contacts | Contact Style | Page Reference |
|--|--|--------------|-------------|-------------------|--------------------|-------------------|----------------|
| Crimp AWG #42-#18 (50 μ inches Gold, BUMP in Plug) Note: Crimp Contacts Sold Separately | DL1-156P | 110535-0000 | DL1 | Plastic Body | 156 Pin Connector | Crimp | 14 |
| | DLM1-156P | 127050-0204 | DLM1 | Metal Body | 156 Pin Connector | Crimp | 16 |
| | DLD1-156P | 111496-0000 | DLD1 | Plastic Body | 156 Pin Connector | Crimp | 19 |
| | DL2-96P | 110777-0000 | DL2 | Plastic Body | 96 Pin Connector | Crimp | 21 |
| | DLM2-96P | 127050-0212 | DLM2 | Metal Body | 96 Pin Connector | Crimp | 23 |
| | DLD2-96P | 111922-0000 | DLD2 | Plastic Body | 96 Pin Connector | Crimp | 26 |
| | DL3-60P | 110900-0008 | DL3 | Plastic Body | 60 Pin Connector | Crimp | 28 |
| | DLM3-60P | 127050-0220 | DLM3 | Metal Body | 60 Pin Connector | Crimp | 30 |
| | DL4-624P | 110959-0002 | DL4 | Metal Frame | 624 Pin Connector | Crimp | 33 |
| | DL4-1248P | 110959-0003 | DL4 | Metal Frame | 1248 Pin Connector | Crimp | ** |
| | DL4-2496P | 110959-0004 | DL4 | Metal Frame | 2496 Pin Connector | Crimp | ** |
| | DL5-260P | 111986-0014 | DL5 | Plastic Body | 260 Pin Connector | Crimp | 35 |
| | DLM5-260P | 127050-0109 | DLM5 | Metal Body | 260 Pin Connector | Crimp | 37 |
| DLM6-360P | 127050-0034 | DLM6 | Metal Body | 360 Pin Connector | Crimp | 40 | |
| Square Post 7,11 (.280) Ext. 50 μ inches Gold, BUMP Std. Square Post \square 0,64 (.025) Factory Installed Solder to PCB Through Hole Interconnect Termination | DL1-156PW6A* | 110535-0030 | DL1 | Plastic Body | 156 Pin Connector | Square Post | 15 |
| | DLM1-156PW6A* | 112134-0000 | DLM1 | Metal Body | 156 Pin Connector | Square Post | 17 |
| | DLD1-156PW6A* | 111496-0002 | DLD1 | Plastic Body | 156 Pin Connector | Square Post | 20 |
| | DL2-96PW6A* | 110777-0025 | DL2 | Plastic Body | 96 Pin Connector | Square Post | 22 |
| | DLM2-96PW6A* | 112136-0000 | DLM2 | Metal Body | 96 Pin Connector | Square Post | 24 |
| | DLD2-96PW6A* | 111922-0002 | DLD2 | Plastic Body | 96 Pin Connector | Square Post | 27 |
| | DL3-60PW6A* | 110900-0014 | DL3 | Plastic Body | 60 Pin Connector | Square Post | 29 |
| | DLM3-60PW6A* | 112138-0000 | DLM3 | Metal Body | 60 Pin Connector | Square Post | 31 |
| | DL4-624PW6A* | 110959-0042 | DL4 | Metal Frame | 624 Pin Connector | Square Post | 34 |
| | DL5-260PW6A* | 111986-0000 | DL5 | Plastic Body | 260 Pin Connector | Square Post | 36 |
| | DLM5-260PW6A* | 112086-0000 | DLM5 | Metal Body | 260 Pin Connector | Square Post | 38 |
| | DLM6-360PW6A* | 111995-0000 | DLM6 | Metal Body | 360 Pin Connector | Square Post | 41 |
| | Square Post 3,18 (.125) Ext. 50 μ inches Gold, BUMP Std. Square Post \square 0,64 (.025) Factory Installed Solder to PCB Through Hole | DL110535-40 | 110535-0040 | DL1 | Plastic Body | 156 Pin Connector | Square Post |
| DLM112134-2 | | 112134-0002 | DLM1 | Metal Body | 156 Pin Connector | Square Post | 17 |
| DLM112136-2 | | 112136-0002 | DLM2 | Metal Body | 96 Pin Connector | Square Post | 24 |
| DLM112138-2 | | 112138-0002 | DLM3 | Metal Body | 60 Pin Connector | Square Post | 31 |
| DLM112086-3 | | 112086-0003 | DLM5 | Metal Body | 260 Pin Connector | Square Post | 38 |
| DLM111995-7 | | 111995-0007 | DLM6 | Metal Body | 360 Pin Connector | Square Post | 41 |
| Wrap Post 15,37 (.605) Ext. 50 μ inches Gold, BUMP Std. Square Post \square 0,64 (.025) Factory Installed | | DL1-156PW4A* | 110535-0025 | DL1 | Plastic Body | 156 Pin Connector | Wrap Post |
| | DLM1-156PW4A* | 112134-0001 | DLM1 | Metal Body | 156 Pin Connector | Wrap Post | 17 |
| | DLD1-156PW4A* | 111496-0001 | DLD1 | Plastic Body | 156 Pin Connector | Wrap Post | 20 |
| | DL2-96PW4A* | 110777-0022 | DL2 | Plastic Body | 96 Pin Connector | Wrap Post | 22 |
| | DLM2-96PW4A* | 112136-0001 | DLM2 | Metal Body | 96 Pin Connector | Wrap Post | 24 |
| | DLD2-96PW4A* | 111922-0001 | DLD2 | Plastic Body | 96 Pin Connector | Wrap Post | 27 |
| | DL3-60PW4A* | 110900-0013 | DL3 | Plastic Body | 60 Pin Connector | Wrap Post | 29 |
| | DLM3-60PW4A* | 112138-0001 | DLM3 | Metal Body | 60 Pin Connector | Wrap Post | 31 |
| | DL4-624PW4A* | 110959-0035 | DL4 | Metal Frame | 624 Pin Connector | Wrap Post | 34 |
| | DL5-260PW4A* | 111986-0003 | DL5 | Plastic Body | 260 Pin Connector | Wrap Post | 36 |
| | DLM5-260PW4A* | 112086-0002 | DLM5 | Metal Body | 260 Pin Connector | Wrap Post | 38 |
| DLM6-360PW4A* | 111995-0001 | DLM6 | Metal Body | 360 Pin Connector | Wrap Post | 41 | |
| Square Post 7,11 (.280) Ext. 20 μ inches Gold, Hermaphroditic Std. Square Post \square 0,64 (.025) Factory Installed Solder to PCB Through Hole | DL1-156PW6 | 110535-0026 | DL1 | Plastic Body | 156 Pin Connector | Square Post | 15 |
| Wrap Post 15,37 (.605) Ext. 20 μ inches Gold, Hermaphroditic Std. Square Post \square 0,64 (.025) Factory Installed | DL1-156PW4 | 110535-0012 | DL1 | Plastic Body | 156 Pin Connector | Wrap Post | 15 |
| | DL2-96PW4 | 110777-0008 | DL2 | Plastic Body | 96 Pin Connector | Wrap Post | 22 |
| | DL3-60PW4 | 110900-0006 | DL3 | Plastic Body | 60 Pin Connector | Wrap Post | 29 |
| | DL4-624PW4 | 110959-0011 | DL4 | Metal Frame | 624 Pin Connector | Wrap Post | 34 |
| PC / RC 4,50 (.177) Ext. 20 μ inches Gold - 4 A max. Round Tail - \varnothing 0,50 (.020) Factory Installed Solder to PCB Through Hole | DLM1-156PC | 127050-0207 | DLM1 | Metal Body | 156 Pin Connector | PC | 18 |
| | DLM2-96PC | 127050-0215 | DLM2 | Metal Body | 96 Pin Connector | PC | 25 |
| | DLM3-60PC | 127050-0223 | DLM3 | Metal Body | 60 Pin Connector | PC | 32 |
| | DLM5-260PC | 127050-0111 | DLM5 | Metal Body | 260 Pin Connector | PC | 39 |
| | DLM6-360PC | 127050-0097 | DLM6 | Metal Body | 360 Pin Connector | PC | 42 |

Note: 50 μ inches gold contacts (Bump on plug side, Flat on receptacle side) are mandatory for applications with less than 100 milliamps.