

Plug-it® Fluorescent Utility Light

Cordless • Cool-Running • Impact-Resistant



CATALOG NUMBER	MAXIMUM BULB SIZE (WATTS)	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
07505.73.05	13	8	1.3	10	079407075058

Product Description:

The impact-resistant Plug-it® Fluorescent Light has a 13-watt bulb that runs cool to the touch when in operation. A cord-locking screw secures the extension cord and resists disconnection when in use.

Product Construction:

- Body:**
 - PVC; yellow
- Lens:**
 - Clear butyrate
- Bulb:**
 - PLS 13-watt fluorescent

Applications:

- Temporary lighting
- For general use only
- Not for use in hazardous locations

Features:

- Turns an extension cord into a light
- Connects to 3-conductor grounded extension cord
- Cool-running 13-watt fluorescent bulb
- Rubberized hood
- Impact-resistant body and lens
- Swivel hook
- Locking screw system assures secure cord connections

Industry Approvals:

- UL Listed

Plug-it® Powr-Center® Adapter

“T” Configuration—Adapt extension cords for different uses



Product Construction:

- Body:**
 - PVC; beige

Applications:

- Adapts a single extension cord for multiple uses

Features:

- 3 convenient outlets

CATALOG NUMBER	VOLTS	AMPS	WATTS	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE	COLOR
04781.96.17	125	15	1875	5	0.6	3	079407047819	Beige

Industry Approvals:

- UL Listed

Powr-Reel™ with 3 Outlets

3-Conductor Grounded • Type SJO • 90°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
44623.61.05	3	16	25	Yellow	125	10	1250	4	2.7	11	079407446230



Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B-174

Insulation:

- Premium-grade, color-coded 90°C EPDM

Jacket:

- CPE; yellow
- Voltage rating: 300 volts

Applications:

- Shop tools

Features:

- Tangle-Proof® instant cord storage
- Sturdy metal reel case
- Rubber cord
- 3 grounded outlets
- Cord locks in place; pull on cord to engage retractable reel

Industry Approvals:

- UL Listed
- OSHA Acceptable

Plug-it® Ground Fault Circuit Interrupter (GFCI) and Surge Protector Plug

CATALOG NUMBER	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
	VOLTS	AMPS	WATTS				
D7524.13.05	125	15	1875	6	0.3	2	079407075249



Product Description:

The Plug-it® Ground Fault Circuit Interrupter and Surge Protector Plug detects power leaks and cuts off electricity in less than one second to prevent electric shock.

Product Construction:

Body:

- PVC; yellow

Applications:

- Use anywhere GFCI protection is desired: job sites, kitchens, bathrooms, garages and workshops

Features:

- Detects power leaks and cuts electricity off in less than a second to prevent electric shock
- Test and reset buttons
- Use with any standard extension cord
- Use indoor or outdoor
- Protects electrical circuitry from voltage fluctuations
- Maximum clamping voltage - 790 volts
- MOV - 80 joules

Industry Approvals:

- UL Listed
- OSHA Acceptable



OSHA Acceptable
Occupational Safety and Health
Administration

