
TEST PRODS

PROD TIPS, CHUCKS AND COLLARS SUPPLIED BRASS NICKEL PLATED. MOLDED THERMO-PLASTIC HANDLES

THREADED - SOLDER TYPE .161 Dia. hole in prod enables use of heavy duty wire 1-3/16 ±1/32 Ø.080 ø3/16 [–] ø3/8 --¹ COLOR Part No. 5-3/16" 01-2604-4-0210 Black 01-2604-4-0212 5-3/16" Red 5-1/2" 6-11/16" Black 01-2604-5-0210 01-2604-5-0212 Red 5-1/2" 6-11/16"


THREADED - SOLDERLESS TYPE

Feed wire thru body, wrap, and secure with knurled collar for solderless connection.




THREADED - SOLDER TYPE

Prode assembles flush with insulating handle




FORCE FIT - SOLDERLESS TYPE

Same as above exept prod tip is force fit into handle rather than threaded




THREADED - PIERCING TYPE

Removable chuck allows for easy needle replacement



Part No. 01-2606-4-0210 01-2606-4-0212 01-2606-5-0210 01-2606-5-0212	A 4" 4" 5-1/2"	B 4-13/16" 4-13/16" 6-5/16"	COLOR Black Red Black Red
01-2606-5-0212	5-1/2"	6-5/16"	Red


DUAL TEST ADAPTER DUAL BANANA PLUG 01-2552-1-0210 (BLK) 01-2552-1-0212 (RED)



Molded nylon, nickel plated brass. Mates with standard dual binding post with 3/4" centers. Polarity indicated on top and side. Can be stacked for multiple connections. Available in red and black.

DUAL TEST ADAPTER BANANA JACKS TO DOUBLE PIN TIP PLUG WITH SETSCREWS 25-2576-1-0210 (BLK)

Rating: 3000 WVDC, 5 Amps.



.750 centers
Double banana jack. .166 Dia.
Brass, nickel plated. Double pin
tip plug. Brass, nickel plated.
Setscrews secure cable and/or
component leads.
Available in ABS black.

