

PATCH CORD - JUMPERS

STACKING CROSS PATCH JUMPERS STANDARD BANANA PLUG BOTH ENDS



AVAILABLE IN 10 COLORS
 795-2219-XX 4 inches
 795-2220-XX 8 inches
 795-2221-XX 12 inches
 795-2231-XX 18 inches
 795-2222-XX 24 inches
 795-2223-XX 36 inches
 795-2224-XX 48 inches
 795-2229-XX 60 inches
 795-2230-XX 72 inches
 Specify Color

1st END - Stacking cross patch standard banana plug. Nickel plated brass body. Nickel plated beryllium copper spring, polypropylene insulation.
WIRE - #18 AWG, stranded copper, PVC insulation.
2nd END - Same as 1st end

INSULATED ALLIGATOR CLIP TO STACKING BANANA PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-2290-XX 4 inches
 795-2291-XX 8 inches
 795-2292-XX 12 inches
 795-2293-XX 24 inches
 795-2294-XX 36 inches
 795-2295-XX 48 inches
 795-2296-XX 60 inches
 Specify Color

1st END - Plated steel alligator clip with vinyl boot.
WIRE - #18 AWG, stranded copper, PVC insulation.
2nd END - Stacking cross patch banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation

MINIATURE STACKING BANANA PLUG BOTH ENDS



AVAILABLE IN 10 COLORS
 795-2365-XX 4 inches
 795-2235-XX 6 inches
 795-2366-XX 8 inches
 795-2236-XX 12 inches
 795-2237-XX 18 inches
 795-2238-XX 24 inches
 795-2367-XX 36 inches
 795-2368-XX 48 inches
 795-2369-XX 60 inches
 Specify Color

1st END - Stacking miniature banana plug. Gold plated brass body. Gold plated beryllium copper spring. Polypropylene insulation.
WIRE - #20 AWG, stranded copper wire, PVC insulation.
2nd END - Same as 1st end

INSULATED MINIATURE ALLIGATOR CLIP TO STACKING BANANA PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-2310-XX 4 inches
 795-2311-XX 8 inches
 795-2312-XX 12 inches
 795-2313-XX 24 inches
 795-2314-XX 36 inches
 795-2315-XX 48 inches
 795-2316-XX 60 inches
 Specify Color

1st END - Plated steel miniature alligator clip with vinyl boot.
WIRE - #20 AWG, stranded copper wire, PVC insulation.
2nd END - Stacking cross patch banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation

STANDARD STACKING BANANA PLUG TO MINIATURE STACKING BANANA PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-2370-XX 12 inches
 795-2371-XX 18 inches
 795-2372-XX 24 inches
 795-2373-XX 36 inches
 795-2374-XX 48 inches
 795-2375-XX 60 inches
 Specify Color

1st END - Stacking cross patch standard banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.
WIRE - #20 AWG, stranded copper wire, PVC insulation.
2nd END - Stacking miniature banana plug. Gold plated brass body. Gold plated beryllium copper spring. Polypropylene insulation.

INSULATED MINI CLIP TO MINIATURE STACKING BANANA PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-2380-XX 12 inches
 795-2381-XX 24 inches
 795-2382-XX 36 inches
 795-2383-XX 48 inches
 795-2384-XX 60 inches
 Specify Color

1st END - Plated steel miniature alligator clip with vinyl boot.
WIRE - #20 AWG, stranded copper wire, PVC insulation.
2nd END - Stacking miniature banana plug. Gold plated brass body. Gold plated beryllium copper spring. Polypropylene insulation

STACKING BANANA PLUG TO TIP PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-5055-XX 4 inches
 795-5056-XX 8 inches
 795-5057-XX 12 inches
 795-5058-XX 18 inches
 795-5059-XX 24 inches
 795-5060-XX 36 inches
 795-5061-XX 48 inches
 795-5062-XX 60 inches
 Specify Color

1st END - Stacking cross patch standard banana plug. Plated brass body. Plated beryllium copper spring. Polypropylene insulation.
WIRE - #20 AWG, stranded copper wire, PVC insulation.
2nd END - Stacking pin tip. Plug gold plated brass body. Gold plated beryllium copper socket. Polypropylene insulation.

INSULATED SPADE LUG TO STACKING BANANA PLUG



AVAILABLE IN (12) RED AND (10) BLACK
 795-2340-XX 12 inches
 795-2341-XX 24 inches
 795-2342-XX 36 inches
 795-2343-XX 48 inches
 795-2344-XX 60 inches
 Specify Color

1st END - Bright tin plated brass spade lug with butyrate insulating handle.
WIRE - #18 AWG, stranded copper wire, PVC insulation.
2nd END - Stacking cross patch standard banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.



BLK	BRN	RED	ORN	YEL	GRN	BLU	PUR	GRY	WHT
10	11	12	13	14	15	16	17	18	19