



HDMI to Composite Video, Stereo Audio and S-Video Converter

Be the first to review this product

NEW

Model: 40-286

HDMI to Composite Video, Stereo Audio and S-Video Converter

LATEST NEWS

Product Slides: [1](#) [2](#) [3](#)

[1](#) [2](#)

- Description
- Technical Resources
- Tags
- Reviews

NEW

40-286 | The 40-286 HDMI converter provides a simple plug and play signal conversion from HDTV HDMI resolutions to legacy composite video and analog stereo signals. Power is supplied from the HDMI source input jack. A external DC power jack is provided with a micro USB jack, a micro USB to USB type 'A' power cable to power the 40-286 is included in the event 5Vdc is not available from the HDMI source. A momentary push button is provided to select between the PAL/NTSC video standards if needed. When a HDMI input signal is not present a TV test pattern is automatically generated to indicate signal loss and to show the device is working on the composite video output.

Specifications:

- Input Video Resolutions: 480p (60Hz), 576p (50Hz), 720p (50Hz/60Hz), 1080i, 1080p (50Hz/60Hz)
- Output Signal: RCA Composite Video (1.0Vpp)
- Output Video Format: NTSC/ PAL (Front Panel Button Selection)
- Output Video Signal Impedance: 75 ohms
- Output Audio: RCA, L & R Stereo Audio
- Support Uncompressed Audio: LPCM
- Maximum Working Current: 320mA
- Power Supply: 5V DC, 1Amp
- Power Adapter: USB (Type A) to (Micro Type B)
- Dimension (in): 2.76 (L) x 2.48 (W) x 0.79 (H)
- Net Weight: 1.41oz

Product Slides: [1](#) [2](#)

Get all the latest information on Events, Sales and Offers. Sign up for newsletter today.

Enter your e-mail Address

SUBMIT

Calrad Electronics has been in the same family ownership for over 60 years. Many of our employees have been with the firm for 25 or more years. Many of our customers have been buying from Calrad for even longer than that. Our manufacturers and suppliers in Asia have known and trusted Calrad for generations. It all started in the 1950's . . .

[Read More >](#)

