

SHOP BY CATEGORY

All Categories

SEARCH

All Products

[Home](#) > Single Channel HD Video, Data Transmitter & Receiver & Power (12V/24V DC/AC), 5.9" Pigtails

3D Products

Model: 95-1052

Single Channel HD Video, Data Transmitter & Receiver & Power (12V/24V DC/AC), 5.9" Pigtails

New Products

Spec Sheets

Personal Info



Single Channel HD Video, Data Transmitter & Receiver & Power (12V/24V DC/AC), 5.9" Pigtails

Item# 95-1052



Click To View
**OUR LATEST
CATALOG 61**



Product Description

Calrad's 95-1052

Video, power & data transmitter and receiver that allows the transmission of real - time CCTV HD video, power and data signal via cost - effective Unshielded Twisted Paired (UTP) cable. Baseband (composite) signals of any type are supported. The 95-1052 is compatible with all HD - TVI, HD - CVI and AHD analog cameras. Used in pairs, the 95-1052 eliminates costly and bulky coaxial cable. The superior interference rejection and low emissions of the 95-1052 allow video signals to coexist in the same wire bundle as telephone, datacom, or low - voltage power circuits, providing access to shared or pre-existing cables. The 95-1052 has a built - in surge suppressor to protect video equipment against damaging voltage spikes. The built-in circuitry provides against crosstalk and noise immunity to ensure the highest quality video signals. (sold in Pairs).

Specifications:

- **UTP Termination:** RJ45 Jack (8 Pin)
- **Cables:** Male BNC plug, Data (RS485, RS422) pigtail, 2.1mm Coax Power Plug, length 5.9"
- **Video Termination:** 75 Ohm Male BNC connector
- **Video Formats:** HD-TVI, HD-CVI, AHD-Analog Signals
- **Video Standards:** NTSC, PAL & SECAM
- **Signal Isolation:** 60db Crosstalk and noise immunity
- **Lightning Protection:** Design Grade III
- **Built-in TVS:** (Transient Voltage Suppressor) for electrical surge protection
- **Housing:** ABS Plastic
- **Size:** Balun Body, L-2.37" x W-1.14" x H-.8"

Distance:

- **HD-TVI 720P analog camera:** Color video max up to 230m (754ft)
- **HD-TVI 1080P analog camera:** Color video max up to 250m (820ft)
- **AHD 720P analog camera:** Color video max up to 320m (1050ft)
- **AHD 960P analog camera:** Color video max up to 330m (1082ft)
- **HD-CVI 720P analog camera:** Color video max up to 440m (1443ft)
- **HD-CVI 1080P analog camera:** Color video max up to 240m (787ft)
- **Data:** 300m (986ft)

Delete Credit/Debit Card
Are you sure you want to delete this card from your saved cards?