



Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

EMI/RFI Filter Products Filters and Accessories

15EEB1 [Active](#)

[Not Reviewed for ELV/RoHS Compliance](#)

(Tyco Electronics P/N: 16090013)

[Search for Parts](#)

Product Documentation - Please use the customer drawing for all design activity.	
Customer Drawing	Drawings & Specifications
No Customer Drawings available at this time.	View All Documents.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info	Pricing Product Availability	Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

Product Photo	Insertion Loss/Specifications
-------------------------------	---

Searchable Features:	
Brand:	Corcom
Product Type:	Power Line
Series:	EEB (1-15 Amp)
Application:	General Purpose
Mount Style:	Flange
Current Rating (Amps.):	15
Terminal Input - Output Combination:	IEC - 1/4" Faston
Filtered:	Yes
Connector Type:	IEC 320/C14
Voltage ? (VAC):	250

Other Properties:	
Approved Standards:	UL Recognized, CSA Certified, SEV Approved, VDE Approved
Facility Installation:	No
Need Min Size With IEC Connector:	Yes
Need Optional Switch, Fusing, Or Voltage Selector:	No
Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (mA):	0.38
Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (mA):	0.22
Terminal Style Output:	Straight

[Copyright and Privacy Statement](#)

[Visit Tyco International, Ltd.](#)