

6609036-9 Product Details

[Share](#) | [Print](#) | [Email](#)


6609036-9

EMI/RFI Filters and Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Filter - EMI/RFI
- Filter Type = Power Line
- SK (3-10 Amp) Series
- General Purpose Application, Switching Power Supply Application
- Mount Style = Flanged

[View all Features](#)

TE Internal Number: 6609036-9

Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • CUSTOMER DRAWING 10VSK1 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • 1-1654250-1_CORCOM_EMI_RFI_QRG (PDF, English) • 1654001_CORCOM_PRODUCT_GUIDE_SK_SERIES (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version B) • 3D Model (IGES, Version B) • 3D Model (STEP, Version B) 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> • Insertion Loss/Specifications <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
---	---

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Filter - EMI/RFI • Filter Type = Power Line • Series = SK (3-10 Amp) • Filtered = Yes <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Current Rating (A) = 10 • Voltage ≤ (VAC) = 250 • Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (mA) = 0.7 • Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (mA) = 0.4 <p>Termination Features:</p> <ul style="list-style-type: none"> • Terminal Input - Output Combination = 1/4" Faston - 1/4" Faston <p>Body Features:</p> <ul style="list-style-type: none"> • Mount Style = Flanged <p>Configuration Features:</p> <ul style="list-style-type: none"> • Fuse Options = None • Fuse Holder Type = North American 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant • Approved Standards = UL Recognized, CSA Certified, VDE Approved <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Facility Installation = No • Need Min Size With IEC Connector = No • Need Optional Switch, Fusing, Or Voltage Selector = No <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = General Purpose, Switching Power Supply <p>Other:</p> <ul style="list-style-type: none"> • Brand = Corcom
---	---

<p>Corporate Information</p> <ul style="list-style-type: none"> About TE Investors News Room Supplier Portal Careers Terms & Conditions Privacy Policy 	<p>Quick Links</p> <ul style="list-style-type: none"> Check Distributor Inventory Cross Reference Products Find Documents & Drawings Product Compliance Support Center Site Map 	<p>Customer Support</p> <ul style="list-style-type: none"> Email or Chat With Us Find a Phone Number Search Knowledge Base Manage Your Account 	<p>Keep Me Informed</p> <p>Receive TE News, Events & Technology Updates</p> <input type="text" value="Enter your email address"/>  
--	---	---	--