

SMD150F/33-2 Product Details



SMD150F/33-2

Raychem Part Number:
E07221-000
✔ [Active](#)

PolySwitch Resettable Devices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Family Name = SMD
- Surface Mount Construction
- IH (Room Temperature) = 1.5 Amps.
- IT (Room Temperature) = 3.00 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SMD150F/33](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL Recognized = 191099-E74889

Electrical Characteristics:

- [IH \(Room Temperature\) \(Amps.\)](#) = 1.5
- [IT \(Room Temperature\) \(Amps.\)](#) = 3.00
- [Vmax Operating \(V\)](#) = 33
- [Rmin \(?\)](#) = 0.08
- [R1 Max \[Post Trip\] \(?\)](#) = 0.23
- [UL Rated Current \(Amps.\)](#) = 40
- Tripped Power Dissipation (Typical) (W) = 1.90

Termination Related Features:

- Construction = Surface Mount

Body Related Features:

- CSA File No. = 1031175 (CA 78165-1)

Contact Related Features:

- [Family Name](#) = SMD

Configuration Related Features:

- [Form Factor \(inches\)](#) = 3425
- [Form Factor \(mm\)](#) = 8763

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041427

Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Related Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem