



2410SFV1.50FM/125-2 Product Details

[Share](#) | [Print](#) | [Email](#)


2410SFV1.50FM/125-2

TE Internal Number: RF1942-000

Active

Fuses

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Type = DC/AC Very Fast Acting Chip Fuse
- Surface Mount Construction
- Form Factor (inches) = 2410
- Form Factor (mm) = 6125
- Rated Current = 1.5 A

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [CP CATALOG 2011-FUSES](#) (PDF, English)

Product Specifications:

- [2410SFV Family \(Marked\)](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Family Name = SFV
- UL Listed = File No. E197536

Electrical Characteristics:

- Rated Current (A) = 1.5
- Cold DCR (Nominal) (Ω) = 0.062
- I^2t (A^2sec)² (Nominal) (Ω) = 1.19
- Interrupt Voltage, Max. (VDC) = 125
- Interrupt Voltage, Max. (VAC) = 125
- Interrupt Current, Max. (A) = 50A@125VAC, 50A@125VDC, 300A@32VDC

Termination Features:

- Construction = Surface Mount

Body Features:

- Type = DC/AC Very Fast Acting Chip Fuse

Configuration Features:

- Form Factor (inches) = 2410
- Form Factor (mm) = 6125

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Environmental:

- Operating Temperature (Max.) ($^{\circ}C$) = 125

Conditions for Usage:

- Min Clear Time @ 100% Rated Current (Hr) = 4
- Min Clear Time @ 200% Rated Current (Seconds) = 0.01

Other:

- Brand = Raychem

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

