



RF2594-000 Product Details

[Share](#) [Print](#) [Email](#)


Active

PolySwitch Resettable Devices

BD540-30

RF2594-000 (BD540-30)

TE Internal Number: RF2594-000

Product Highlights [View All](#)

- Automotive Application
- Family Name = BD
- Vmax = 16 V
- Imax = 100 A
- Rmin = .0016 Ω

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Family Name BD

Electrical Characteristics

Vmax (V) 16

Imax (A) 100

Rmin (Ω) 0.0016

Rmax (Ω) 0.0044

Power Dissipation (Typical) (W) 6.20

Termination Features

Construction Radial

Configuration Features

Coating Cap

Industry Standards

RoHS/ELV Compliance RoHS compliant, ELV compliant

Lead Free Solder Processes Not relevant for lead free process

RoHS/ELV Compliance History Always was RoHS compliant

Operation/Application

Application Automotive

Packaging Features

Packaging Method Bag/Box

Other

Brand Raychem

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

