



# Pliers

Home > 6" Long Chain Nose Solid Joint Side Cutting Pliers

## 6" Long Chain Nose Solid Joint Side Cutting Pliers

Catalog Number: 6546CVSMLNN



[0] Write a review

[Ask a question](#)

BUY NOW



[Download Images](#)

Share: [f](#) [t](#) [p](#)

### Overview

6-5/8" Long Chain Nose Side Cutting Solid Joint Pliers, Cushion Grip

### Features

- 6" Long Chain Nose Solid Joint Side Cutting Pliers
  - Designed for Reaching Confined Areas
  - Long Chain Nose with Fine Serrated Jaws to Make Wire Loops and Bends
  - Electronically Induction Hardened Hand-Honed, Keen Side Cutting Edges
  - Made of Forged Alloy Tool Steel
  - Individually Tested for Strength and Cutting Ability
  - Polished Head
  - Red Double Dipped Cushion Handle Grips
  - Spring Keeps Jaws Open

### Specifications

Foreign Trade Code	8203206030
UPC	037103324078
Set	No
Overall Length	6.625 in
Handle Material	Double Dip Cushion Grip
Edge Type/Cut Capacity	Std./14 AWG
Jaw Length	1-7/8 in
Jaw Thickness	3/8 in
Jaw Width	11/16 in
Packaging	No
Weight (Catalog)	0.380 lb

[+ Reviews | Questions](#)



Trusted by the Trades.

MERCHANDISE

Apex Tool Group

910 Ridgebrook Road

Suite 200

Sparks, Maryland 21152

(800) 821-8814

[Tools](#)

[Brands](#)

[New Products](#)

[Featured Products](#)

[Shipping Information](#)

[Where to Buy](#)

[Media Center](#)

[About](#)

[Warranty](#)

[Contact Us](#)

[Privacy Policy](#)

[California And Nevada  
Privacy Notice](#)

[Distributor Login](#)

[Reseller Policies](#)

