

CW INDUSTRIES
 130 James Way
 Southampton, PA 18966
 Phone: 215-355-7080 • Fax: 215-355-1088
 Email: info@cwind.com • Website: <http://www.cwind.com>

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [Header Connectors](#) > [Header Connectors](#) > Item # CWN-300-26-0000

IMAGE
NOT
AVAILABLE



Item # CWN-300-26-0000, Header Connectors

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock	DIGI-KEY MOUSER
-------------------------	--

Specifications

Style	IDC
Connector Type	Header
Mounting	3-wall
Plating	10µ in. Gold Over 50µ in. Nickel
Polarization	Polarization Ribs
Number of Contacts	26
Terminal	Right Angle 0.090" for 1/16" Boards
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	Greater Than 5 x 10 ⁹ ohms
Listing Agency (Consult drawing or factory for specific rating)¹	 Listed Agencies
Compliance	

¹ Due to ongoing advancements, additional agency certifications may be available, contact us for more information.

[Print](#) [Back](#)