





**Item # CWN-350-14-0000, Header Connectors**

[Check Distributor Stock](#) · [Specifications](#)

**Check Distributor Stock**

Check Distributor Stock	<a href="#">DIGI-KEY</a> <a href="#">MOUSER</a>
-------------------------	--

**Specifications**

<b>Style</b>	IDC
<b>Connector Type</b>	Header
<b>Mounting</b>	3-wall
<b>Plating</b>	10µ in. Gold Over 50µ in. Nickel
<b>Polarization</b>	Polarization Ribs
<b>Number of Contacts</b>	14
<b>Terminal</b>	Straight 0.090" for 1/16" Boards
<b>Contacts</b>	Phosphor Bronze Standard
<b>Insulator Material</b>	UL 94V-0 Flame Retardant Thermoplastic
<b>Color</b>	Blue
<b>Operating Temperature</b>	-55 to +125 °C
<b>Maximum Current Rating (Per Contact)</b>	1 A
<b>Dielectric Withstand Voltage</b>	Greater Than 500 VDC at Sea Level
<b>Insulation Resistance</b>	Greater Than 5 x 10 <sup>9</sup> ohms
<b>Listing Agency (Consult drawing or factory for specific rating)<sup>1</sup></b>	 Listed Agencies
<b>Compliance</b>	

<sup>1</sup> Due to ongoing advancements, additional agency certifications may be available, contact us for more information.