



PRODUCTS & SERVICES:

Switches ▶

Indicator Lights ▶

Connectors ▶

Defense/Aerospace  
Connectors ▶

Contract  
Manufacturing ▶

Custom Assembly ▶

Custom Switches and  
Connectors ▶

Search Catalog

By Keyword

All Categories  PCB Connectors

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [PCB Connectors](#) > Item # CWR-142-34-0203

[Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # CWR-142-34-0203, PCB Connectors



[larger image](#)

MORE IMAGES

- Features of PCB Connectors
- Contact Drawing for PCB Connectors
- Strain Relief for PCB Connectors
- Cover Lip for PCB Connectors
- Assembly for PCB Connectors
- Assembly for PCB Connectors-1
- Detailed Dimensional Drawing for PCB Connectors
- How to Order PCB Cable Assemblies

DOWNLOADS

- Dim Dwg CWR-142-XX-0203 (PDF, 643KB)

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock [DIGI-KEY](#) [MOUSER](#)

Specifications

Style	IDC
Mounting	Without Strain Relief for Daisy Chain termination
Plating	Tin
Number of Contacts	34
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	Greater Than 5 x 10 <sup>9</sup> ohms
Minimum Cover Pull-Off Force (Force Along Contacts Primary Axes)	Without Strain Relief 15 lb
Compliance	

Request Information

