



PRODUCTS & SERVICES:

Switches >

Indicator Lights >

Connectors >

Defense/Aerospace  
Connectors >

Contract  
Manufacturing >

Custom Assembly >

Custom Switches and  
Connectors >



Search Catalog

By Keyword

All Categories  Card Edge Connectors

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [Card Edge Connectors](#) > Item # CWR-170-10-0203

[Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # CWR-170-10-0203, Card Edge Connectors




[larger image](#)

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock [DIGI-KEY](#) [MOUSER](#)

Specifications

Style	IDC
Mounting	Without Mounting Ears
Terminal	For 1/32" and 1/16" Boards
Plating	Tin
Number of Contacts	10
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	5 x 10 <sup>9</sup> ohms
Minimum Cover Pull-Off Force (Force Along Contacts Primary Axes)	8 oz/contact
Compliance	

Request Information

MORE IMAGES

- Features of Card Edge Connectors
- Contact Drawing for Card Edge Connectors
- Detailed Dimensional Drawing for Card Edge Connectors

DOWNLOADS

Dim Dwg CWR-170-XX-0203 (PDF, 578KB)

Plastic Key for Card Edge Connector



[Plastic Key for Card Edge Connector](#)