



PRODUCTS & SERVICES:

Switches >

Indicator Lights >

Connectors >

Defense/Aerospace
Connectors >

Contract
Manufacturing >

Custom Assembly >

Custom Switches and
Connectors >

Search Catalog

By Keyword


All Categories Socket Connectors

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [Socket Connectors](#) > Item # CWR-220-10-0203

[Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # CWR-220-10-0203, Socket Connectors



larger image

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock [DIGI-KEY](#) [MOUSER](#)

Specifications

Style	IDC
Connector Type	Socket
Mounting	Without Strain Relief
Plating	Tin
Polarization	Polarization Slots
Number of Contacts	10
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Strain Relief Strap Material	Insulated Stainless Steel
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	Greater Than 5 x 10 ⁹ ohms
Typical Withdrawal Force	2-8 oz/contact
Minimum Cover Pull-Off Force (Force Along Contacts Primary Axes)	8 oz/contact
Compliance	

Request Information

MORE IMAGES

- Features of Socket Connectors
- Socket Connectors with Metal Strain Relief Strap
- Socket Connectors with Non-Strain Relief Cover
- Contact Drawing for Socket Connectors
- Polarization Drawing of Socket Connectors
- Polarization Method Drawing of Socket Connectors
- How to Order Socket Cable Assemblies

DOWNLOADS

Dim Dwg CWR-220-XX-0203 (PDF, 513KB)

Plastic Key for Socket Connectors



[Plastic Key for Socket Connector](#)

