



[larger image](#)

Item # GRB238B801BRRL1Z, GRB Series Full Size Sealed Rocker Switches
 List Price QUOTE

[Check Distributor Stock](#) · [Specifications](#) · [Materials](#) · [Technical Information](#)

Check Distributor Stock

Check Distributor Stock	PEERLESS ELECTRONICS DIGI-KEY MOUSER
-------------------------	--

Specifications

Circuitry	SPST
Switch Function	ON-OFF LED
Electrical Ratings	16A 12VDC
IP Level	65
Mounting	21 x 35
Actuator Color	Red
Housing Color	Black
Polarization	N
Actuator Legend	None
Illumination	Illuminated
Terminal	0.250 Quick Connect (SQ)
Fitting	Snap-In

Options



Reference Lamp Chart
[larger image](#)

Optional Connector	Not Available
--------------------	---------------

Compliance



Materials

Frame Material	Nylon (UL: 94V-2)
Actuator Material	Nylon (UL: 94V-2) PC (UL: 94V-2)
Terminal Material	Copper Alloy

Technical Information

Operating Temperature	-25 to 85 °C
Maximum Contact Resistance	50m ohm
Minimum Insulation Resistance	DC 500VM 100M OHM
Dielectric Strength (AC) (1 Minute)	1500 °C
Mechanical Life	> 100,000 Cycles
Maximum Solderability of Terminals (Per 3 Seconds)	350 °C

[Print](#) [Back](#)