

home



PHENOLIC


more four arm knobs >>

Material- Phenolic
Insert- Brass
Projecting Stud- Steel, zinc plated


THE FOUR ARM




Threaded Insert



Threaded Insert Thru Hole



Projecting Stud



Threaded Insert

Part No.	Insert	
	Thread	Depth
2820-A	5/16-18	1/2
2820-B	3/8-16	1/2
2820	1/4-20	3/8
1"B"=1-1/8, "D"=5/8 2"B"=1-5/32, "D"=21/32		

Threaded Insert Thru Hole

Part No.	Insert	
	Thread	Depth
2820AT	1/4-20	3/8
2820AU	5/16-18	1/2
2820AV	3/8-16	1/2
3"B"=1-1/8, "D"=5/8		

Projecting Stud

Part	Stud	Max

No.	Thread	Length	Length
2820-G	5/16-18	1	4-1/2
2820-J	1/4-20	1	4-1/2
2820-T	5/16-18	1-1/4	4-1/2
2820-Y	5/16-18	1-3/4	4-1/2

[<< back](#)