

home



PHENOLIC


more four arm knobs >>

Material- Phenolic
Insert- Brass
Projecting Stud- Steel, zinc plated


THE FOUR ARM




Threaded Insert



Threaded Insert Thru Hole



Projecting Stud



Threaded Insert

Part No.	Insert	
	Thread	Depth
2830-A	5/16-18	1/2
2830-B	3/8-16	1/2
2830-V	3/8-24	5/8
2830BG¹ +	1/2-13	5/8
2830BH²	1/2-20	5/8
2830	1/4-20	3/8

1 "B" = 1-1/8, "D" = 5/8
2 "B" = 1-5/32, "D" = 21/32

Threaded Insert Thru Hole

Part No.	Insert	
	Thread	Depth
2830BJ	3/8-16	1/2
2830BK	3/8-24	5/8
2830BL³	1/2-13	5/8
2830BM³	1/2-20	5/8

2830CA	5/16-18	1/2
3"B"=1-1/8, "D"=5/8		

Projecting Stud

Part No.	Stud		Max Length
	Thread	Length	
2830-D	5/16-18	1/2	3-1/2
2830-E	3/8-16	1	3-1/2
2830-T	3/8-16	1-1/2	3-1/2
2830-U	3/8-16	2	3-1/2
2830AG	3/8-16	2-1/2	3-1/2
2830CG	1/2-13	3/4	3-1/2

← back