

home



**PHENOLIC**

more three arm knobs >>

**Material-** Phenolic  
**Insert-** Brass  
**Projecting Stud-** Steel, zinc plated




**Threaded Insert**

| Part No.               | Insert  |       |
|------------------------|---------|-------|
|                        | Thread  | Depth |
| <a href="#">3035AU</a> | 5/16-18 | 1/2   |
| <a href="#">3035AX</a> | 1/4-20  | 3/8   |
| <a href="#">3035AY</a> | 10-32   | 3/8   |


**Threaded Insert Thru Hole**

| Part No.                           | Insert  |       |
|------------------------------------|---------|-------|
|                                    | Thread  | Depth |
| <a href="#">3035JD<sup>3</sup></a> | 1/4-20  | 3/8   |
| <a href="#">3035JE<sup>3</sup></a> | 5/16-18 | 1/2   |
| <b>3 "B" = 3/4, "D" = 1/8</b>      |         |       |


THE THREE ARM



Threaded Insert Thru Hole



Projecting Stud



### Projecting Stud

| Part No.   | Stud    |        | Max Length |
|--|---------|--------|------------|
|  | Thread  | Length |            |
| <a href="#">3035AQ<sup>2</sup></a>                   | 5/16-18 | 3/4    | 4-1/2      |
| <a href="#">3035AS</a>                               | 1/4-20  | 9/16   | 4-1/2      |
| <a href="#">3035AW</a>                               | 1/4-20  | 3/4    | 4-1/2      |
| <a href="#">3035BG</a>                               | 5/16-18 | 3/4    | 4-1/2      |
| 1" "B" = 5/8, "D" = 1/8<br>2" "B" = 1-1/4, "D" = 5/8 |         |        |            |

[← back](#)