

TWO-SHOT INSTRUMENT CONTROL KNOB

Series #1227

- ▶ Control knobs and levers in thermoplastic, with or without flange and index/graduations.
- ▶ Knobs can be decorated or customized to your specific need.
- ▶ Perfect knobs for synthesizers and other electronic applications.
- ▶ A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.
- ▶ A wide range of soft touch control knobs available in thermoplastic overmold.
- ▶ Colors available upon request.
- ▶ Please note: Not all variations available are listed below. Please **contact customer service** to inquire about all available options.



CHECK INVENTORY

REQUEST A QUOTE

Item #	Diameter A	Height B	Indicator Line	Inlay	Material Type	Mounting Diameter	Mounting Type	Set Screw Thread	Color	Product Drawing
1227-D	0.6	0.85	Yes	No	Thermoplastic Elastomer	0.19	Plain Molded Hole		Black	Download
1227-F	0.6	0.85	Yes	No	Thermoplastic Elastomer	0.25	Plain Molded Hole		Black	Download
1227-H	0.6	0.85	Yes	No	Thermoplastic Elastomer	0.25	Interference Fit		Black	Download
1227-J	15mm	21mm	Yes	No	Thermoplastic Elastomer	M6 flatted to M4.5	Interference Fit		Black	Download
1227-K	0.6	0.85	Yes	No	Thermoplastic Elastomer	0.25 Flatted to 0.16	Interference Fit		Black	Download
1227-L	15mm	21mm	Yes	No	Thermoplastic Elastomer	6mm	Interference Fit		Black	Download

PRODUCTS

- Knobs
- Handles
- Electronic Enclosures
- Hex Hybrid Standoffs
- Two-Shot / Soft Touch
- Frac Balls
- Cable Glands
- Rubber Grommets
- Custom Molding

RESOURCES

- Product Sell Sheets
- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Blog
- Careers

QUESTIONS

- Contact Us
- Request a Quote

