

Home / Panel Mount Indicators / LED Panel Mount Indicator Green 11/16" Dome 12V Tab Terminal



LED Panel Mount Indicator Green 11/16" Dome 12V Tab Terminal



SKU: 1116-G12-CW

Categories: [Panel Mount Indicators](#), [LED Panel Mount Indicator](#)

Product Description

PMI LED 18mm 12V Tab Green MS



Description

Stock Availability

Technical Downloads

Additional Information

Terminals	<i>Tab Terminals – Quick connect</i>
LED size	–
Mounting Hole Dimension	<i>Dia. 0.688"</i>
Mounting Type	<i>Front Panel Mount</i>
PMI Color	<i>Green</i>
PMI Lens Color	<i>Waterclear</i>
Lens Shape	<i>Dome Lens</i>
LED Output Color	<i>Green</i>

Lamp Type	<i>LED</i>
Luminous Intensity Typ. (mcd)	<i>2400 mcd</i>
Peak Wavelength (nm)	<i>520 nm</i>
Voltage	<i>12 Volts</i>
LED Voltage Forward Typ. (V)	<i>12.0 V</i>
LED Voltage Forward Min. (V)	<i>12 V</i>
LED Voltage Forward Max. (V)	<i>14 V</i>
Operation Supply Voltage	<i>12V</i>
Rated Current	<i>15 mA</i>
Wire Gauge	<i>–</i>
PMI Housing Finish	<i>Black</i>
Bezel Finish	<i>No Bezel</i>
Material Lens	<i>Polycarbonate</i>
MSL Rating	<i>–</i>
RoHS	<i>Yes</i>
REACH Compliant	<i>Yes</i>
Conflict Mineral Free	<i>Yes</i>
Harmonization Code	<i>8531.80.90.51</i>
ECCN	<i>EAR99</i>
Country of Origin	<i>MX (Mexico)</i>
Product Status	<i>Active</i>



© 2021 Visual Communications Company, LLC
Contact Sales 1.800.522.5546

