



# DH SERIES

## GENERAL PURPOSE FILTERS

### INTRODUCTIONS

DE & DH Series filters are for UL 544 & UL 2601 health care equipment.

### COMPONENTS

PART NO.	Cx (uF)	L (mH)
06DHEG3H	0.015	0.55
06DHEG3V		
06DHAG5		

### MINIMUM INSERTION LOSS IN dB

COMMON MODE (L-G) IN 50 OHM SYSTEM						
TYPE	CURRENT RATING	FREQUENCY-MHz				
		0.15	0.15	0.15	0.15	0.15
06DHEG3H	6A	12	15	20	22	15
06DHEG3V	6A	12	15	18	20	18
06DHAG5	6A	10	15	18	20	18

### MECHANICAL CONSTRUCTION



EG3H



EG3V



AG5

### SPECIFICATIONS

- Maximum leakage current each line-to-ground: @ 115VAC 60Hz: 2uA @ 250VAC 50Hz: 5uA
- Hipot rating (one minute) line-to-ground: 2250VDC line-to-line: 1450VDC
- Operating frequency: 50/60Hz
- Rated voltage: 115/250VAC

### ELECTRICAL SCHEMATIC

