



SEARCH FANS AND BLOWERS BY PARAMETERS

Length x Width(mm): ALL
 Thickness(mm): ALL
 Voltage: ALL
 Air Flow(CFM): ALL
 Air Pressure (inchH₂O): ALL
 Noise(dB-A): ALL
 IP Rated: ALL
 Product Number:

Filter results by:
 Tachometer
 Rotation Signal
 PWM

Other Manufacturer Products

Part Number	Supplier	Dimension	V.Range	Voltage	Bearing	Current(A)	Power(W)	Speed	Noise	Air Flow	Air Pressu
<u>TFA0412CN-CN</u>	DELTA	40 X 40 X 28		12V	ball	0.6	7.2	17600	55	25	1.87

Part Number	Dimension	Voltage	V.Range	Bearing	Current(A)	Power(W)	Speed	Noise	Air Flow	Air Pressu
<u>TFA0412CN-CN</u>	40X40X28	12	7.0~13.2	ball	0.6	7.2	17600	55	25	1.87
<u>FFB0412UHN-CA07</u>	40X40X28	12	10.8~13.2	ball	0.6	7.2	18000	58	25	1.98
<u>FFB0412UHN-SP4Z</u>	40X40X28	12	7.0~13.2	ball	0.84	10.08	23000	59.9	27	3.15
<u>FFB0412SHN</u>	40X40X28	12	4.5~13.8	ball	0.5	6	13000	54.5	24	1.07
<u>FFB0412SHN-B</u>	40X40X28	12	4.5~13.8	ball	0.5	6	13000	54.5	24	1.07
<u>FFB0412SHN-F00</u>	40X40X28	12	4.5~13.8	ball	0.5	6	13000	54.5	24	1.07
<u>FFB0412SHN-R00</u>	40X40X28	12	4.5~13.8	ball	0.5	6	13000	54.5	24	1.07
<u>FFB0412UHN-C</u>	40X40X28	12	5.5 ~13.2	ball	0.65	7.8	18500	58.5	27	2.11
<u>FFB0412UHN-CF00</u>	40X40X28	12	5.5 ~13.2	ball	0.65	7.8	18500	58.5	27	2.11
<u>FFB0412UHN-CR00</u>	40X40X28	12	5.5 ~13.2	ball	0.65	7.8	18500	58.5	27	2.11

SEARCH FANS AND BLOWERS BY OTHER MANUFACTURER PART NUMBER