



Data Sheet

page 1 of 2

#D171204

EYECAP Insulated Terminal Cap - Type B, SIT

Retroactive from 19, July

Around January 2018, data will be updated upon UL registration

No	Item Description	B	b	D	L	A	T	AWG
1	EYECAP-SIT(B)25R	8.60	13.9	9.0	25.3	9.9	1.0	6.0~4.0
2	EYECAP-SIT(B)25B	8.60	13.9	9.0	25.3	9.9	1.0	6.0~4.0
3	EYECAP-SIT(B)25Y	8.60	13.9	9.0	25.3	9.9	1.0	6.0~4.0
4	EYECAP-SIT(B)25G	8.60	13.9	9.0	25.3	9.9	1.0	6.0~4.0
5	EYECAP-SIT(B)25BK	8.60	13.9	9.0	25.3	9.9	1.0	6.0~4.0
6	EYECAP-SIT(B)35R	10.20	15.5	10.5	27.5	10.1	1.1	4.0~3.0
7	EYECAP-SIT(B)35B	10.20	15.5	10.5	27.5	10.1	1.1	4.0~3.0
8	EYECAP-SIT(B)35Y	10.20	15.5	10.5	27.5	10.1	1.1	4.0~3.0
9	EYECAP-SIT(B)35G	10.20	15.5	10.5	27.5	10.1	1.1	4.0~3.0
10	EYECAP-SIT(B)35BK	10.20	15.5	10.5	27.5	10.1	1.1	4.0~3.0
11	EYECAP-SIT(B)50R	11.60	17.2	11.5	43.2	12.2	1.20	2.0~1.0
12	EYECAP-SIT(B)50B	11.60	17.2	11.5	43.2	12.2	1.20	2.0~1.0
13	EYECAP-SIT(B)50Y	11.60	17.2	11.5	43.2	12.2	1.20	2.0~1.0
14	EYECAP-SIT(B)50G	11.60	17.2	11.5	43.2	12.2	1.20	2.0~1.0
15	EYECAP-SIT(B)50BK	11.60	17.2	11.5	43.2	12.2	1.20	2.0~1.0
16	EYECAP-SIT(B)70R	13.80	20.3	13.9	48.2	12.3	1.50	1/0~1.0
17	EYECAP-SIT(B)70B	13.80	20.3	13.9	48.2	12.3	1.50	1/0~1.0
18	EYECAP-SIT(B)70Y	13.80	20.3	13.9	48.2	12.3	1.50	1/0~1.0
19	EYECAP-SIT(B)70G	13.80	20.3	13.9	48.2	12.3	1.50	1/0~1.0
20	EYECAP-SIT(B)70BK	13.80	20.3	13.9	48.2	12.3	1.50	1/0~1.0
21	EYECAP-SIT(B)95R	16.50	22.8	16.0	56.2	18.8	1.60	2/0~1/0
22	EYECAP-SIT(B)95B	16.50	22.8	16.0	56.2	18.8	1.60	2/0~1/0
23	EYECAP-SIT(B)95Y	16.50	22.8	16.0	56.2	18.8	1.60	2/0~1/0
24	EYECAP-SIT(B)95G	16.50	22.8	16.0	56.2	18.8	1.60	2/0~1/0
25	EYECAP-SIT(B)95BK	16.50	22.8	16.0	56.2	18.8	1.60	2/0~1/0
26	EYECAP-SIT(B)120R	18.30	24.6	18.0	61.6	18.8	1.60	4/0~3/0
27	EYECAP-SIT(B)120B	18.30	24.6	18.0	61.6	18.8	1.60	4/0~3/0
28	EYECAP-SIT(B)120Y	18.30	24.6	18.0	61.6	18.8	1.60	4/0~3/0
29	EYECAP-SIT(B)120G	18.30	24.6	18.0	61.6	18.8	1.60	4/0~3/0
30	EYECAP-SIT(B)120BK	18.30	24.6	18.0	61.6	18.8	1.60	4/0~3/0
31	EYECAP-SIT(B)150R	20.80	27.2	21.4	66.7	22.5	1.70	250Kcmil~4/0
32	EYECAP-SIT(B)150B	20.80	27.2	21.4	66.7	22.5	1.70	250Kcmil~4/0
33	EYECAP-SIT(B)150Y	20.80	27.2	21.4	66.7	22.5	1.70	250Kcmil~4/0
34	EYECAP-SIT(B)150G	20.80	27.2	21.4	66.7	22.5	1.70	250Kcmil~4/0
35	EYECAP-SIT(B)150BK	20.80	27.2	21.4	66.7	22.5	1.70	250Kcmil~4/0
36	EYECAP-SIT(B)185R	22.10	31.0	22.7	74.0	23.2	1.80	300~250Kcmil
37	EYECAP-SIT(B)185B	22.10	31.0	22.7	74.0	23.2	1.80	300~250Kcmil
38	EYECAP-SIT(B)185Y	22.10	31.0	22.7	74.0	23.2	1.80	300~250Kcmil
39	EYECAP-SIT(B)185G	22.10	31.0	22.7	74.0	23.2	1.80	300~250Kcmil
40	EYECAP-SIT(B)185BK	22.10	31.0	22.7	74.0	23.2	1.80	300~250Kcmil
41	EYECAP-SIT(B)240R	28.10	35.1	26.8	83.0	25.5	1.80	400~350Kcmil
42	EYECAP-SIT(B)240B	28.10	35.1	26.8	83.0	25.5	1.80	400~350Kcmil
43	EYECAP-SIT(B)240Y	28.10	35.1	26.8	83.0	25.5	1.80	400~350Kcmil
44	EYECAP-SIT(B)240G	28.10	35.1	26.8	83.0	25.5	1.80	400~350Kcmil
45	EYECAP-SIT(B)240BK	28.10	35.1	26.8	83.0	25.5	1.80	400~350Kcmil
46	EYECAP-SIT(B)300R	29.00	37.0	28.2	95.1	25.5	1.90	500~450Kcmil
47	EYECAP-SIT(B)300B	29.00	37.0	28.2	95.1	25.5	1.90	500~450Kcmil
48	EYECAP-SIT(B)300Y	29.00	37.0	28.2	95.1	25.5	1.90	500~450Kcmil
49	EYECAP-SIT(B)300G	29.00	37.0	28.2	95.1	25.5	1.90	500~450Kcmil
50	EYECAP-SIT(B)300BK	29.00	37.0	28.2	95.1	25.5	1.90	500~450Kcmil

EyeCap International Ltd.

Address:#2008 Windstone., 79 nonhyunro, Seocho-ku, Seoul, Korea/S. 06775

Tel. +82-(0)70-4137-4205 Fax. +82-(0)504-062-7968

Email:jessica.lee@eyecapinternational.com

Bank name: KB KOOKMIN BANK

Beneficiary: EyeCap International Ltd.

Bank a/c no. 787268-11-007074(SWIFT code CZNBKRSE)

Tax reg. no. 124-87-47904

51	EYECAP-SIT(B)400R	32.50	40.9	32.8	96.9	25.7	2.10	650~550Kcmil
52	EYECAP-SIT(B)400B	32.50	40.9	32.8	96.9	25.7	2.10	650~550Kcmil
53	EYECAP-SIT(B)400Y	32.50	40.9	32.8	96.9	25.7	2.10	650~550Kcmil
54	EYECAP-SIT(B)400G	32.50	40.9	32.8	96.9	25.7	2.10	650~550Kcmil
55	EYECAP-SIT(B)400BK	32.50	40.9	32.8	96.9	25.7	2.10	650~550Kcmil

T- Average thickness $\pm 10\%$

All other dimensions are restricted to $\pm 15\%$ tolerance.

EYECAP-SIT(B) 1.5 BK

① ② ③

① TYPE: (A) (Solderless terminal lugs type)
(B) (Tubular terminal lugs type)

② SIZE : 1.5mm² ~ 300 mm²

③ COLOR : BK(Black), R(Red),BL(Blue),Y(Yellow), G(Green)



