

### FL-603 **LED Flexible Flashlight**

- Sturdy anodized aluminum construction, 13.6" hands free flexible arm attachment
- Flexible cable extension that can be bent and twisted into any shape or angle
- White light brightly illuminates even the tightest work areas
- Two-way tail cap switch allows for twist on/off capability or push and hold functionality
- Ideal for auto repair, workshop or home DIY use and more









Auto repair

Electrical check


White light illuminates the tightest work areas

Light source	Illumination	Cable size	Handle size	Battery
White LED	11000mcd	Ø5mm x 13.6"	Ø15mm x 6.9"	1.5V AAA x 3pcs (not included)

· Individual packing: Blister card

#### ► CE-027 **Pin Extractors**

- Designed for use with various connectors such as MOLEX, AMP, TYCO, etc
- 5 different size insertion tools
- Available individually or as a set of 5 in a pouch











Put the pin extractor into housing

Push the plunger of pin extractor

Extract the pin

Model No.	L	DØ	dØ	(D-d)/2	Remark
902-394	0.45"	0.150"	0.122"	0.014"	-
902-395	0.57"	0.106"	0.085"	0.011"	Inter-locking
902-396	0.50"	0.157"	0.110"	0.023"	-
902-397	0.79"	0.126"	0.102"	0.012"	V.35 male
902-398	0.67"	0.130"	0.110"	0.008"	V.35 female
	Individual pa		Blister	card	

• CE-0275 Contents: One each of five extractors above. Comes in plastic carrying pouch.




CONNECTORS

#### 900-150/900-151/900-202 **Measuring Tape**



- Blade with Nylon coating for easy scale reading and avoiding light reflection.
- Magnetic end-hook for convenient measuring.
- Anti-slip and shockproof rubber case.
- · Hi-rel power tape.









Model No.	L (Max.)	W (Max.)	Individual packing
900-150	5M/16ft	23.0mm/0.91"	Blister card
900-151	7.5M/25ft	24.5mm/0.96"	Blister card
900-202	7.5M/25ft	32.0mm/1.26"	Blister card

#### ▶ 400-044 **6" Digital Caliper**

- · Hardened stainless steel.
- High quality 6"(150mm), thumb wheel for accuracy and ease with 4 measurement: inside, outside, depth and step.
- Precision-ground and lapped measuring surface.





Depth diameter

measurement





Inside diameter measurement

Outside diameter measurement

Material	Range	Accuracy	Individual packing
AISI430	0~150mm/0~6"	±0.01mm/0.0005"	Plastic box + Color label sleeve

# PD-155 9" Torpedo Level


- · Lightweight and compact
- With magnet for hands-free work
- Provides accurate readings, including horizontal, vertical and 45-degree angles.
- Easy-to-read with fluorescent green gauges



Material	3 vials	OAL	Individual packing
ABS plastic construction	45°, 90° & 180°	220mm/9"	Blister card

# 900-019 **5 PCS Needle File Set**






Material	HRC	Cut length	Handle O.D.	OAL	Individual packing
SKS-8	60°	75mm/ 3.0"	Ø 5mm/ Ø 0.2"	170mm/ 6.7"	Pouch

### ▶ 900-216 **5 PCS Needle File Set**





Material	HRC	Cut length	Handle O.D.	OAL	Individual packing
SKS-8	60°	85mm/ 3.3"	Ø 7mm/ Ø 0.28"	180mm/ 7.1"	Pouch

• 840 tie points

900-247

- · Round hole designed for easy plug and pull
- Expandable by combining several boards together to meet your different requirement
- · Wearproof material made of ABS & phosphor bronze with good flexibility and electric conductivity


**Round Hole Bread Board** 



**Excellent expandability** 



Individual packing Blister card Friendly graduations



#### **Round Hole Bread Board** 900-248/900-249



#### Application:

Used as a simulated layout for R&D and students. Features:


- · Round hole designed for easy plug and pull
- Expandable by combining several boards together to meet your different requirement
- Wearproof material made of ABS & phoshor bronze with good flexibility and electric conductivity





Edge plate can easily fold up

Model No.	Tie points	Individual packing
900-248	1580	Blister card
900-249	2420	Blister card



**TAIWAN PATENT NO. 215526 CHINA PATENT ZL 03231122.2** 

#### **Bread Board Accessory** 900-271/900-272



- 70 pcs of 22 AWG solid wires Pre-cut, pre stripped and pre-formed on each end
- Variety of colors
- · Completely reusable
- 14 lengths x 5 pcs each
- (2, 5, 7, 10, 12, 15, 17, 20, 22, 25, 50, 75, 100 and 125mm)



Case Size (mm/inch)	Individual packing
165x55x15/ 6.5x2.2x0.6	Poly bag + Hanger

- 350pcs of 22 AWG solid wires
- Pre-cut, pre stripped and pre-formed on each end
- · Variety of colors
- Completely reusable
- 14 lengths x 25 pcs each
- (2, 5, 7, 10, 12, 15, 17, 20, 22, 25, 50, 75, 100 and 125mm)



178x90x28/ 7x3.5x1.1	Poly bag + Hanger
Case Size (mm/inch)	Individual packing

#### ► 900-032 PLCC Extractor










RoHS COMPLIANT







A spring assisted chip carrier extraction tool, specially designed for the safe removal of PLCC's from sockets without damage to component parts.



Material OAL (mm
aterial OAL (mm 10 + POM 145x76/

# > 900-094 **3-Pronged Parts Grabber**

· Plunger opens prongs





Individual packing
Blister card

#### **▶** 900-258 **IC Extractor**




Stainless steel construction for removing dual in-line IC packages. (Insulated vinyl grip.)



Individual packing
Blister card

#### 900-238 Vacuum Pick-Up Tool





- The hand-held SMD vacuum pick-up tool is ideal for picking up and moving electronic components, large or small. With fountain pen dimensions, it fits easily into your hand or pocket.
- The new high-power probes have longer holding action.

#### Function

 Lightweight, portable and suitable for picking and placing small components weighing up to 50 grams and having a flat surface, dilly packages and surface mount components, etc.

Individual packing

Color box

### 902-115 Vacuum Pick-Up Tool













#### Function:

- The hand-held SMD vacuum pick up tool is ideal for picking up and moving large or small electronic components.
- Lightweight, portable and suitable for the picking and placing small components weight to up 50 grams and having a flat surface, dilly packages and surface mount components, etc.
   The new high-power probes have longer holding action.



# Index

### 900-103 Inspection Mirror



- All-angle ball joint mirror with stainless steel back.
- Visual inspection of hidden areas.
- Double ball joint links swivel mirrors for viewing to 360°.
- · Made of tempered spring steel to move freely and hold desired position.
- Replaceable, plated, copper-backed, clear-view mirror.
- · Non-rotating inner hex rods prevent mirror from swinging out of alignment.
- · Insulating vinyl grip.




Lens size	OAL (mm/inch)	Individual packing	
50x90mm (2"x3.5")	216 ~ 490 / 8.5"~19.3"	Blister card	





#### 900-255 Inspection Mirror



Lens size	178~505mm	Individual packing
Ø32mm (1.25")	(7.9"~19.9")	Blister card




#### MS-322 Telescopic Magnetic Pick-Up Tool



- · A handy chrome plated telescopic magnetic retrieving tool.
- · Ideal for hard-to-reach working.
- Extension length: max. 450mm(17.7")
- Maximum pick-up: 590g(1.3lb)









#### 900-212 **Telescoping Magnetic Pick-up Tool**



- Strong pick up force of 9 lbs.
- · Allows access to "hard-to-reach" parts.
- Telescopes from 6-1/2" to 25-5/8"



Individual packing Blister card

### 800-070 **Magnetizer Demagnetizer**



- · A convenient pocket sized tool, housed in a strong plastic case.
- · Ideal for the general magnetizer demagnetizer of small hand tool i.e screwdriver, hexagon keys.





Individual packing

### 800-039

### 20 in 1 Screwdriver With Telescoping Pick-Up Tool





- (A) Regular screwdriver with 13-pcs. screw bits 5-pcs. sockets and 1-pcs socket adaptor fits all kinds of job.
- (B) Telescoping magnetic pick-up tool (up to 17-1/2" long/440mm) stored inside the tube pulling out to pick up small metal objects.

Individual packing Blister card



#### 900-205 **4 PCS Probe Set**




- 4pcs stainless steel single-ended probe that can be used for all kinds of precision work in electronics.
- · Hook, curved, straight and angle tips 4 types packed in a vinyl pouch.

AISI 410	Straight:145/5.7 Angled:140/5.5	Pouch
Material	OAL (mm/inch)	Individual packing

# 







· Can grab small spring and wires.

Model No.	Material	OAL (mm/inch)	Individual packing
902-070	AISI 410	205/8	Distance
902-073	+ PVC	205/8	Blister card

### 902-256/902-257 **Push-button Pick-up Tool**











Open the jaws Pick up the object easily

- 900-256: Push-Button Pick-Up Tool has a 265mm /10.4"flexible stem with a small set of jaws at one end.
- 900-257: Long Push-Button Pick-Up Tool has a 600mm /23.6"flexible stem with a small set of jaws at one end.
- · Ideal for home, shop, garage, work place etc.

Individual packing Blister card

# 902-255 Long Pick-up Tool with Magnet Tip







picking up small metallic objects from inaccessible areas.

• Long Pick-Up Tool with Magnet Tip is an extendable magnetic tool for

#### 902-255 (620mm/24.4")



Pick up small metallic objects from inaccessible areas

- This Pick-Up Tool has a 620mm/24.4" flexible stem with a strong magnet at • Powerful magnet lifts 1.5KG
- · Ideal for home, shop, garage, work place etc.

Individual packing

Blister card

#### 902-117 **Multi-Angle Swivel-Actions Vacu-Vise**




- Suction areas must be smooth, flat and clean.
   Adding a little water under vacuum base is recommended.
- Swivels 360° and tilts 90° to desired angle.
- 2.8" (70mm) metal jaws open to 2.7" (68mm).
- Equipped with slide-on rubber jaw for fragile work.
- 6 1/4" (158mm) triangular base.
- · Aluminum die-cast construction.
- · Light weight and durable.

Replacement Jaw	Individual packing
902-117-JAWS	Plain box+Color label



#### **Hobby Vise** 900-049



### 902-116 **6 In 1 Mini Hammer**





• The 6 in 1 mini hammer with six different interchangeable heads: two round steel, one flat brass, one flat plastic and one tinner's steel.

185/7.3	Blister card
OAL(mm/inch)	Individual packing

#### PD-372 Mini Vise



# 900-179 Heavy Duty Curved-Claw



Handle: Fiberglass, S45C	454g (16 oz/1 lb)	330/13	Tag
Material	Weight	OAL (mm/inch)	Individual packing

### 







Model No.	Material	Туре	OAL (mm/inch)	Individual packing
900-058		C4:	130/5"	
900-181	AISI 410	Straight	160/6"	Blister card
900-222			155/6"	Caru



### ▶ 900-254 Blowing Brush

• Clean blowing air effectively clears.
• Ideal for blowing hard-to-reach areas.



#### 900-270 Mini Vacuum Cleaner





### **900-251/900-252/900-253 Liquid Dispenser Bottles**



- Polyethylene bottles are not chemically reactive
- Purity pump to prevent backwash of contaminants into container



900-253

900-252

900-251



Model No.	Description	Individual packing
900-251	4 oz/114 ml	Poly bag + Hanger
900-252	6 oz/170 ml	Poly bag + Hanger
900-253	8 oz/227 ml	Poly bag + Hanger

### ▶ 900-230 Flux Bottle



• Dispenses flux evenly with a fine tipped needle.

#### 900-158 Automa

# **Automatic Center Punch**



PE	ø37x122/ø1.5x4.8	Poly bag + Hanger (2 pcs/pack)
Material	OAL. (mm/inch)	Individual packing





н	ss	133/5.2	Blister card
Tip M	laterial	OAL (mm/inch)	Individual packing

### ▶ 900-177 Multi-Fuse Puller

- Shock-proof durable plastic
- Serrated grip design to prevent slipping
- Safely removes 0~200A/250V and 0~100A/600V Cartridge fuses



Individual packing

Blister card