


MAGNIFICATION & LIGHTING



www.eclipsetools.com

Headband Magnifier

- Flexible lenses combination for higher magnification.
- Detachable LED light device.The tilt degree of LED light is adjustable.
- · Thumb screw to adjust the tilt degree of lens.



Description	Part No.
Headband Magnifier 2X(4D) / 3X(8D) / 6X(20D)	MA-016

Lighted Visor Magnifier 2/3/6X

- Flip-down Lenses
- · Loupe flips out of the way when not in use



Description	Part No.
Lighted Visor Magnifier 2X(4D) / 3X(8D) / 6X(20D)	900-128

"OptiVisor" Binocular Magnifier

- · Reduces eve strain
- Optical glass (not plastic) lenses
- · Genuine leather comfort band







Complete OptiVisor	Magnification	Lense Plate Only
900-079	1.5X @ 20"	900-236
900-082	1.75X @ 14"	900-096
900-081	2X @ 10"	900-147A
900-075	2.5X @ 8"	900-075A
900-063	2.75X @ 6"	900-076
900-235	3.5X @ 4"	900-077

900-142 OptiVisor with No Lens

"OptiLoupe" 2X Magnifier



Description	Part No.
"OptiLoupe" 2X Magnifier	900-064

VisorLight



- · Clips onto headband of Optivisor
- Xenon laser for illuminating close-up work

Description	Part No.
VisorLight (Headband shown but not included)	900-080
Replacement bulb for Visorlight	900-080B

Economy Visor Magnifier 4X



Description	Part No.
Economy Visor Magnifier 4X	900-127

Protective Glasses

 Ideal for use when cutting, grinding or boring to protect the eyes against flying particles.



Description	Part No.
Protective Glasses	900-167

Magnifier Sheet

• Hold over any subject matter to magnify 3X(8D)~4X(13D)



Description	Part No.
Magnifier Sheet	900-239

Sliding Magnifier



- 3X(8D) / 6X(20D) Magnification
- · Lenses slide in for storage

Description	Part No.
Sliding Magnifier	900-123

Magnifier

• 4X(13D) / 7.5X(26D) Magnification

· Lenses slide in for storage



Description	Part No.
Magnifier	900-124

Lighted Magnifier - Round



Description	Part No.
Lighted Magnifier - Round	900-125
Replacement Bulb	900-125B

Lighted Magnifier - Rectangular



• 2X(5D) with 4X(12D) round insert

LED Illuminated Magnifier



Description	Part No.
LED Illuminated Magnifier	902-239

Description Part No. Lighted Magnifier - Rectangular 900-126


Magnifier-Round-Hand-Held

- · Glass lens with ergo handle.
- · Ideal for very small objects and documents reading.



Description	Part No.
Magnifier-Round-Hand-Held	902-238

Handheld Metal Magnifier





Description	Part No.
Handheld Metal Magnifier	MA-017

2X (2.5D) Foldable Magnifier (ø 5")

· Glass lens with adjustable folding arms design.

· Sits on a desk or table and adjusts for varying height and angle.

· Great for working on hobbies, documents, and circuit boards, etc.



Helping Hands Clip-on Magnifier

· Zinc alloy Handle, acrylic lens, compact,

2 LED Lights
• Lens dia: 4.3" main lens, 0.83" inset lens

Clip-On Design Base

Magnification: 2X(4D) main lens, 4X(12D) inset lens

· Battery: 1.5V x 3 AAA



Part No.	

902-240

Description	Part No.
Helping Hands Clip-on Magnifier	MA-018

2X (3D) / 4X (12D) Desk Type Magnifier

Description

- Light Source: AC120V 60Hz T4 12W circular fluorescent lamp Supplied with Electronic ballast Product size: Height 14-1/2"

2X(2.5D) Foldable Magnifier (Ø 5")








Description	Lens size (inchØ)	Part No.
2X(3D) / 4X(12D) Desk Type Magnifier	3-5/16	902-108
Replacement Bulb		Bulb-T4



2X (5D) Portable Magnifier Lamp

- Easy swivel lens that rotates 360° and tilts 280°
- Powerful 2X(5D) magnifying lens
- 12W fluorescent lamp
- · Adjustable joint arm for easy positioning
- Energy efficient and super brightLiftable lens-protection cover



Size	Base: 7x5.9 inch Height: 14.56 inch
Weight (lbs)	3.04
Color	Black

Description	Part No.
5D Portable Magnifier Lamp	902-221
Replacement Bulb	Bulb-T4



Gooseneck Magnifier Lamp









- 2X(5D) magnification glass lens.
- Even, shadow-free light under the magnifying lens with 22-watt T5 circular fluorescent tube will make it easier for you to see and enjoy the activities longer.

 The flexible gooseneck allows you to angle and point the light to where you need it most.

 Clamps easily and securely onto most flat surfaces up to 2.6" thick.

- Dust-proof cover for lens protection.

Description	Part No.
Gooseneck Magnifier Lamp	902-110
Replacement Bulb	Bulb-T5



Table Clamp Magnifier With Workbench Lamp



Magnifier Workbench Lamp

- 2X(5D) magnification glass lens.
 Even, shadow-free light under the magnifying lens with 22-watt circular fluorescent tube makes it easier
- for you to see and enjoy the activities longer.
 Spring balanced adjustable arm for easy maneuverability and positioning.
- · Heavy duty cast bench clamp mounts to
- any bench top.

 Adjustable clamp base fits up to 65mm thick surfaces.
- Comes with a protection cover to produce sharp images over a wide viewing area.











Description	Part No.
Magnifier Workbench Lamp (110V)	900-061
Magnifier Workbench Lamp (220V)	900-061C
Magnifier Workbench Lamp-Black (110V)	8PK-F1205CA-B
Lens for 900-061 Lamp (Optional)	900-061-3X
Light Bulb for 900-061	900-061B

LED Wind Up Flashlight

- Save \$\$\$\$ on batteries
- Environmentally friendly-no battery waste.
- · Generate power anytime, anywhere
- Self powered electronics, 3V and 6V DC plug-ins included for household charging.
- Ergonomic grip design. 1 minute winding gives over 30 minutes of light from the LED.
- · Ideal for emergency conditions, camping, fishing, garage work, and it's always ready.
- · Operate in 2 modes 1 LED, 4 LED's.
- Super bright light output.

Description	Part No.
LED Wind Up Flashlight	902-223



6 LED's Technology Flashlight





Description	Part No.
6 LED's Technology Flashlight	900-182

LED Flashlight



- · Rugged design aluminum body contoured for firm grip.
- Light weight and easy to carry.
 Operated using 2x AA cell batteries (not included).
 Switch on/off control on the bottom.
- · Black color.

Description	Size	Part No.
LED Flashlight	11/16x6-1/8	902-068
Replacement Bulb		902-068B

Flashlight



- O.A.L.: 6" 2AA Batteries, not included

Description		Color	Part No.
0000	Flashlight 10 LED	Silver	902-044

15 LED 2-Stage LED Flashlight



- 15 LED lamps provide powerful illumination & extended battery life
- · Narrow beam & floodlight options
- Three position switchKnurled no-slip handle



Description	Part No.
15 LED 2-Stage LED Flashlight	902-244